

Product availability: Stock - Normally stocked in distribution facility

Main

Range	D10S
Product	Disconnect Switch
Line Rated Current	200 A
Horsepower Rating	25 hp 120 V AC 50 hp 200/240 V AC 100 hp 480 V AC 100 hp 600 V AC
System Voltage	600 V AC
Mounting Type	Door
NEMA Size	4
Service Entrance Rated	Not service entrance rated

Ordering and shipping details

Category	22642 - DISCONNECT SWITCHES - D10
Discount Schedule	T
GTIN	00785901118633
Nbr. of units in pkg.	1
Package weight(Lbs)	8.9700000000000006
Returnability	Y
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[D10S4](#)