

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

| | |
|---------------------------|----------------------|
| Range of product | Harmony 9001SK |
| Product or component type | Selector switch |
| Device short name | 9001SK |
| Type of operator | Maintained |
| Operator profile | Gloved hand knob red |

Complementary

| | |
|-------------------------------|--------------------------|
| Bezel material | Plastic |
| Mounting diameter | 1.18 in (30 mm) |
| Product weight | 0.13 lb(US) (0.059 kg) |
| Shape of signaling unit head | Round |
| Operator position information | 3 positions |
| Contacts type and composition | Without contact block |
| Mechanical durability | 500000 cycles |
| Light block supply | Via integral transformer |
| Light source | Incandescent |
| Bulb base | BA 9s |
| [Us] rated supply voltage | 110...120 V AC 50/60 Hz |
| Compatibility code | 9001SK |

Environment

| | |
|---------------------------------------|--|
| Protective treatment | TC |
| Ambient air temperature for storage | -40...158 °F (-40...70 °C) |
| Ambient air temperature for operation | -13...158 °F (-25...70 °C) |
| Electrical shock protection class | Class II conforming to IEC 61140 |
| IP degree of protection | IP66 conforming to IEC 60529 |
| NEMA degree of protection | NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4 NEMA 4X NEMA 6 |
| Standards | EN/IEC 60947-1 EN/IEC 60947-5-1 EN/IEC 60947-5-4 JIS C 4520 JIS C 852 UL 508 CSA C22.2 No 14 |
| Product certifications | NEMA UL 508 |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

| | |
|----------------------|---|
| Vibration resistance | 7 gn (f = 2...500 Hz) conforming to IEC 60068-2-6 |
| Shock resistance | 50 gn conforming to IEC 60068-2-27 |

Ordering and shipping details

| | |
|-----------------------|---------------------|
| Category | 21429 - 9001 SK,SKY |
| Discount Schedule | CS1 |
| GTIN | 00785901463146 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.5 |
| Returnability | N |
| Country of origin | MX |

Offer Sustainability

| | |
|---------------------------|--|
| California proposition 65 | WARNING: This product can expose you to chemicals including: |
| ----- Substance 1 | Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. |
| ----- More information | For more information go to www.p65warnings.ca.gov |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9001SK42J1FR](#)