

Product availability: Non-Stock - Not normally stocked in distribution facility



### Main

|                           |                 |
|---------------------------|-----------------|
| Range of product          | Harmony 9001SK  |
| Product or component type | Selector switch |
| Device short name         | 9001SK          |
| Type of operator          | maintained      |

### Complementary

|                               |                          |
|-------------------------------|--------------------------|
| Bezel material                | Plastic                  |
| Mounting diameter             | 1.18 in (30 mm)          |
| Net weight                    | 0.13 lb(US) (0.059 kg)   |
| Shape of signaling unit head  | Round                    |
| Operator position information | 4 positions              |
| Contacts type and composition | Without contact block    |
| Mechanical durability         | 500000 cycles            |
| Light block supply            | Via integral transformer |
| Light source                  | incandescent             |
| Bulb base                     | BA 9s                    |
| [Us] rated supply voltage     | 110...120 V AC 50/60 Hz  |
| Compatibility code            | 9001SK                   |

### Environment

|                                       |                                                                                                                |
|---------------------------------------|----------------------------------------------------------------------------------------------------------------|
| Protective treatment                  | TC                                                                                                             |
| Ambient air temperature for storage   | -40...158 °F (-40...70 °C)                                                                                     |
| Ambient air temperature for operation | -13...158 °F (-25...70 °C)                                                                                     |
| Electrical shock protection class     | Class II IEC 61140                                                                                             |
| IP degree of protection               | IP66 IEC 60529                                                                                                 |
| NEMA degree of protection             | NEMA 1<br>NEMA 12<br>NEMA 13<br>NEMA 2<br>NEMA 3<br>NEMA 3R<br>NEMA 4<br>NEMA 4X<br>NEMA 6                     |
| Standards                             | EN/IEC 60947-5-1<br>UL 508<br>EN/IEC 60947-1<br>EN/IEC 60947-5-4<br>JIS C 4520<br>JIS C 852<br>CSA C22.2 No 14 |
| Product certifications                | NEMA<br>UL 508                                                                                                 |

|                      |                               |
|----------------------|-------------------------------|
| Vibration resistance | 7 gn 2...500 Hz)IEC 60068-2-6 |
| Shock resistance     | 50 gn IEC 60068-2-27          |

## Ordering and shipping details

|                     |                      |
|---------------------|----------------------|
| Category            | 21429 - 9001 SK,SKY  |
| Discount Schedule   | CS1                  |
| GTIN                | 00785901348214       |
| Package weight(Lbs) | 0.23 kg (0.5 lb(US)) |
| Returnability       | No                   |
| Country of origin   | MX                   |

## Offer Sustainability

|                            |                                                                                                                                                                                                                                                                       |
|----------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                                                                                                                                                                 |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                                                                                                                                                                                                     |
| REACH free of SVHC         | Yes                                                                                                                                                                                                                                                                   |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>                                                                                                                                                                        |
| Mercury free               | Yes                                                                                                                                                                                                                                                                   |
| RoHS exemption information | <a href="#">Yes</a>                                                                                                                                                                                                                                                   |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>                                                                                                                                                                                                                                |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                                                                                                                                                                                                         |
| Circularity Profile        | No need of specific recycling operations                                                                                                                                                                                                                              |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.                                                                                                                                          |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9001SK88J1](#)