

Product data sheet

Characteristics

ZB4BW0G513

22mm push button, Harmony ZB4, metal base, yellow 110/120VAC 50/60Hz LED light module, 1NO contact, faston terminals



Main

Range of product	Harmony XB4
Product or Component Type	Light block
Device short name	ZB4
[Us] rated supply voltage	120 V
Head type	Standard
Light source colour	Orange

Complementary

Sale per indivisible quantity	1
Fixing collar material	Zamak
Compatibility code	ZB4

Environment

Ambient Air Temperature for Operation	-40...158 °F (-40...70 °C)
---------------------------------------	----------------------------

Ordering and shipping details

Category	22469 - PUSHBUTTON,22MM ACCESSORIES-NEW
Discount Schedule	CS2
GTIN	3606480499432
Nbr. of units in pkg.	1
Package weight(Lbs)	2.86 oz (81 g)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.24 in (5.7 cm)
Package 1 width	1.26 in (3.2 cm)
Package 1 Length	1.89 in (4.8 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
RECh Regulation	RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration

Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ZB4BW0G513](#)