



Main

Range of Product	Harmony XD2
Product or Component Type	Complete joystick controller
Device short name	XD2
Mounting diameter	1.18 in (30 mm)
Bezel material	Chromium plated metal

Complementary

Operator position information	All positions
Notch per direction	1...2
Operator direction information	8 directions
Contacts type and composition	1 C/O snap action 2 C/O snap action
Short-circuit protection	10 A gG (gl) Neozed cartridge fuse EN/IEC 60947-5-1
Connections - terminals	Captive screw clamp terminals, 2 x 1.5 mm ² with or without cable end Captive screw clamp terminals, 1 x 2.5 mm ² with or without cable end
Electrical durability	1000000 Cycles, AC-15 230 V 3600 cyc/h 0.5 EN/IEC 60947-5-1 appendix C 1000000 Cycles, AC-15 127 V 3600 cyc/h 0.5 EN/IEC 60947-5-1 appendix C 1000000 Cycles, DC-13 24 V 3600 cyc/h 0.5 EN/IEC 60947-5-1 appendix C 1000000 Cycles, DC-13 48 V 3600 cyc/h 0.5 EN/IEC 60947-5-1 appendix C 1000000 Cycles, DC-13 120 V 3600 cyc/h 0.5 EN/IEC 60947-5-1 appendix C 1000000 cycles, AC-15 48 V 3600 cyc/h 0.5 EN/IEC 60947-5-1 appendix C
Contact code designation	A600-Q600
Overvoltage category	Class I IEC 61140
Mechanical durability	1000000 cycles
Fixing center	100 x 100 mm
Return	To 0 position
Height	5.00 in (127 mm)
Depth	3.58 in (91 mm)
Net Weight	0.66 lb(US) (0.3 kg)

Environment

Standards	EN/IEC 60947-5-1
Product Certifications	CSA DEMKO GL
Protective treatment	TC
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Vibration resistance	25 gn 10...500 Hz)IEC 60068-2-6
Shock resistance	50 gn IEC 60068-2-27
IP degree of protection	IP65 IEC 60529

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

Category	22476 - JOYSTICKS (NOT CRANE)
Discount Schedule	I
GTIN	3389110316483
Nbr. of units in pkg.	1
Package weight(Lbs)	12.42 oz (352 g)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.70 in (9.4 cm)
Package 1 width	7.09 in (18 cm)
Package 1 Length	3.86 in (9.8 cm)
Unit Type of Package 2	S03
Number of Units in Package 2	10
Package 2 Weight	8.98 lb(US) (4.075 kg)
Package 2 Height	11.81 in (30 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XD2EC1111](#)