



### Main

Product or Component Type	Full voltage starter
Range of Product	Instakits
Starter Type	Non reversing

### Complementary

Control Circuit Voltage	240 V AC 50/60 Hz
Current Rating	40 A AC-1 25 A AC-3
Horsepower Rating	2 Hp 120 V AC, 1 phase 3 Hp 240 V AC, 1 phase 7.5 Hp 208 V AC, 3 phase 7.5 Hp 230 V AC, 3 phase 15 Hp 460 V AC, 3 phase 20 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Auxiliary Contacts	1 NO + 1 NC
Location of connection	Line
Height	10.04 in (255 mm)
Depth	7.01 in (178 mm)
Width	6.77 in (172 mm)

### Environment

Product Certifications	UL IEC CSA
Enclosure Type	NEMA 1 painted sheet steel

### Ordering and shipping details

Category	22313 - CTRS,D-LINE,ENCL (METAL)
Discount Schedule	I11
GTIN	785901757061
Nbr. of units in pkg.	1
Package weight(Lbs)	10.47 lb(US) (4.75 kg)
Returnability	Yes
Country of origin	MX

### Packing Units

Unit Type of Package 1	PCE
Package 1 Height	9.49 in (24.1 cm)
Package 1 width	10.51 in (26.7 cm)
Package 1 Length	14.69 in (37.3 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
PVC free	Yes

## Contractual warranty

Warranty	18 months
----------	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[LE1D253A62OU70](#)