



Main

Product or Component Type	Full voltage starter
Range of Product	Instakits
Starter Type	Non reversing

Complementary

Control Circuit Voltage	240 V AC 50/60 Hz
Current Rating	40 A AC-3 60 A AC-1
Horsepower Rating	5 Hp 240 V AC, 1 phase 10 Hp 208 V AC, 3 phase 10 Hp 230 V AC, 3 phase 3 Hp 120 V AC, 1 phase 30 Hp 460 V AC, 3 phase 30 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Auxiliary Contacts	1 NO + 1 NC
Location of connection	Line
Height	13.98 in (355 mm)
Depth	7.40 in (188 mm)
Width	10.63 in (270 mm)

Environment

Product Certifications	CSA IEC UL
Enclosure Type	NEMA 1 painted sheet steel

Ordering and shipping details

Category	22313 - CTRS,D-LINE,ENCL (METAL)
Discount Schedule	I11
GTIN	785901800187
Nbr. of units in pkg.	1
Package weight(Lbs)	50.00 lb(US) (22.68 kg)
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	13.98 in (35.5 cm)
Package 1 width	10.63 in (27 cm)
Package 1 Length	7.40 in (18.8 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[LE1D403A62OU70](#)