



Main

Device short name	LK3
Disconnecter device type	Non-fusible disconnect switch

Complementary

Line Rated Current	600 A
Depth	6.56 in (166.62 mm)
Electrical connection	Lugs on kit
Height	12.63 in (320.80 mm)
Maximum Horse Power Rating	200 Hp 240 V AC 350 Hp 480 V AC 400 hp 600 V AC
Mounting support	Panel Rail
Number of poles	3
Permissible voltage	600 V AC
Shaft cross section	15 x 15 mm
Width	11 in (279.40 mm)

Environment

Product Certifications	CE UL listed file E191104 CCN WP2X CSA LR703149 class 4652 04
------------------------	---

Ordering and shipping details

Category	22640 - IEC DISCONNECT-GS1,LK3
Discount Schedule	I11
GTIN	00785901179962
Nbr. of units in pkg.	1
Package weight(Lbs)	18.63 lb(US) (8.45 kg)
Returnability	No
Country of origin	FR

Packing Units

Package 1 Height	2.100 dm
Package 1 width	5.000 dm
Package 1 Length	4.000 dm

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[LK3SU3](#)