

HMIYPSOMAC1

AC / DC power adapter for HMIPSO and HMIDAD

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range of product	Magelis iPC
Product or component type	External power supply module
Accessory / separate part category	Electrical accessory

Complementary

Accessory / separate part destination	Magelis HMIPSP Magelis HMIPSO Magelis HMIDAD
Input voltage	90...260 V AC at 47...63 Hz
Input current	1600 mA at 100 V AC
Output voltage	24 V DC
Line Rated Current	2.62 A
Inrush current	70 A at 230 V AC

Environment

Ambient air temperature for operation	0...70 °C
Ambient air temperature for storage	-40...185 °F (-40...85 °C)
Relative humidity	0...95 % non-condensing
Product certifications	UL 60950 CULus CSA 60950 CE

Ordering and shipping details

Category	22575 - MAGELIS MC3
Discount Schedule	MC3
GTIN	00785901518853
Nbr. of units in pkg.	1
Package weight(Lbs)	2.2000000000000002
Returnability	N
Country of origin	TW

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1604 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[HMIYPSOMAC1](#)