

# ZCKE625

limit switch head ZCKE - steel roller plunger -  
+120 °C



Product availability: Non-Stock - Not normally stocked in distribution facility



## Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKE
Head type	Plunger head
Product compatibility	XCKJ
Associated body	ZCKJ41H29 ZCKJ21 ZCKJ41H7 ZCKJ8H29 ZCKJ6H29 ZCKJ8 ZCKJ11H29 ZCKJD35H7 ZCKJ5 ZCKJD39H29 ZCKJ9H7 ZCKJ4H29 ZCKJ8H7 ZCKJD37H7 ZCKJ5H7 ZCKJ7 ZCKJD37H29 ZCKJ2H7 ZCKJ7H7 ZCKJ11H7 ZCKJ21H7 ZCKJD35H29 ZCKJ7H29 ZCKJ1H7 ZCKJ41 ZCKJD39 ZCKJ9H29 ZCKJD31H7 ZCKJD37 ZCKJ2 ZCKJD31H29 ZCKJ11 ZCKJ4 ZCKJ1H29 ZCKJD39H7 ZCKJ1 ZCKJ6H7 ZCKJ6 ZCKJD31 ZCKJ4H7 ZCKJD35 ZCKJ9 ZCKJ21H29 ZCKJ2H29 ZCKJ5H29
Movement of operating head	Linear
Type of operator	Roller plunger spring return metal
Type of approach	Lateral approach 2 directions

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Complementary

Switch actuation	By 30° cam
Positive opening	With
Product weight	0.34 lb(US) (0.155 kg)
Head material	Metal

## Environment

Ambient air temperature for operation	50...248 °F (10...120 °C)
Ambient air temperature for storage	50...248 °F (10...120 °C)
Environmental characteristic	High temperature

## Ordering and shipping details

Category	22411 - LIMIT SWITCHES,IEC,XCKJ
Discount Schedule	T
GTIN	00785901277620
Nbr. of units in pkg.	1
Package weight(Lbs)	0.34000000000000002
Returnability	N
Country of origin	FR

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1440 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ZCKE625](#)