

Complementary

Line Rated Current	55 A
AWG gauge	AWG 6...AWG 1/0
Depth	7 in (177.80 mm)
Electrical Connection	Screw clamp terminal
Height	5.3 in (134.62 mm)
Permissible voltage	600 V AC
Net Weight	27 lb(US) (12.25 kg)
Protection Type	Harmonic distortion Overvoltage protection Current protection
Width	9 in (228.60 mm)

Environment

NEMA Degree of Protection	No enclosure rating (open device)
Product certifications	UL listed file E180243 CSA LR29753 CE

Ordering and shipping details

Category	22062-LINE REACTORS/FILTERS (RL,KLC)
Discount Schedule	CP4C
GTIN	00785901712237
Package weight(Lbs)	28.00 lb(US) (12.701 kg)
Returnability	No
Country of origin	US

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[RL05502](#)