

## Main

Bezel material	Black plastic
Device short name	SK
Enclosure type	Weatherproof enclosure dust and oil resistant indoor/outdoor Enclosure corrosion resistance indoor/outdoor
Mounting diameter	1.18 in (30 mm)

## Complementary

Line Rated Current	10 A
Cap/operator or lens colour	Black
Contact operation	Standard fingersafe
Contacts type and composition	2 NO + 2 NC
Control type	Push-button
Electrical connection	Screw clamp terminal
Mounting support	Panel
Operator position information	3 positions
Operator profile	Gloved hand knob
Operator profile	1 projecting push-button
Permissible voltage	<= 600 V
Shape	Round head
Type of operator	Maintained
Utilisation category	AC-15 DC-13

## Environment

NEMA degree of protection	NEMA 1/2/3/3R/4/4X/6/12/13
product certifications	CE UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03

## Contractual warranty

Warranty period	18 months
-----------------	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Schneider Electric:

[9001SKS44FBH2](#)