



Main

Range	TeSys
Device short name	LUF
Product or Component Type	Function module
Product Compatibility	LUCCLUCMLUCBLUCD

Complementary

Mounting Mode	Plug-in
Mounting Location	Front side
Main function available	Indication of motor load
[Us] rated supply voltage	24 V DC
Analogue output current	4...20 mA
Type of output signal	Value of I average/I _r ratio within the range of 0 to 2 for LUCB and LUCD Value of I average/I _r ratio within the range of 0 to 3 for LUCC
Load impedance ohmic	100 Ohm typical <= 500 Ohm
Measurement accuracy	+/- 10 % with multifunction control unit 1 % of I _r +/- 6 % with advanced control unit
Connection pitch	0.15 in (3.81 mm)
Connections - terminals	Screw clamp terminals 1 0.00...0.00 in ² (0.14...1 mm ²) flexible without cable end Screw clamp terminals 1 0.00...0.00 in ² (0.14...1 mm ²) rigid without cable end Screw clamp terminals 1 0.00...0.00 in ² (0.25...0.5 mm ²) flexible with cable end Screw clamp terminals 1 0.00...0.00 in ² (0.25...1 mm ²) flexible with cable end Screw clamp terminals 2 0.00...0.00 in ² (0.14...0.5 mm ²) rigid without cable end Screw clamp terminals 2 0.00...0.00 in ² (0.14...0.75 mm ²) flexible without cable end Screw clamp terminals 2 0.00...0.00 in ² (0.25...0.34 mm ²) flexible with cable end Screw clamp terminals 2 0.00 in ² (0.5 mm ²) flexible with cable end
Associated cable type	AWG 26...AWG 16
Tightening torque	1.77...2.21 lbf.in (0.2...0.25 N.m) 0.10 in (2.5 mm) flat
Net Weight	0.11 lb(US) (0.05 kg)

Ordering and shipping details

Category	22399 - TESYS U, ACCESSORIES
Discount Schedule	I11
GTIN	3389110365498
Nbr. of units in pkg.	1
Package weight(Lbs)	1.83 oz (52 g)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.30 in (3.3 cm)
Package 1 width	1.85 in (4.7 cm)
Package 1 Length	3.74 in (9.5 cm)
Unit Type of Package 2	S01
Number of Units in Package 2	36
Package 2 Weight	4.61 lb(US) (2.09 kg)
Package 2 Height	5.91 in (15 cm)
Package 2 width	5.91 in (15 cm)
Package 2 Length	15.75 in (40 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[LUFV2](#)