



LEAD FINISH: SILVER	
BUSHING FINISH: SILVER	
CAPACITANCE	.050 $\mu$ F MIN.
TEMP. RANGE	-55°C TO 125°C
CURRENT	23 10 AMP MAX.
WORKING VOLTAGE	100 VDC MAX.
D.C. RESISTANCE	.01ohms MAX.
MIN. I.L. PER MIL-STD-220 AT 25°C NO LOAD	
FREQ. MHz	I.L. (db)
1	--
10	36
100	45
1 GHz	60
SCHEMATIC 	
MARKING: PART: 563 BAG: 54-790-023 DATE CODE QTY/BAG (200 MAX.)	

- NOTES:  
 1. MAXIMUM MOUNTING TORQUE = 1.5lb-in.  
 2. HARDWARE IS INCLUDED.

		23	22	REV. NO.	TOLERANCES UNLESS OTHERWISE SPECIFIED	 SPECTRUM CONTROL INC.	ERIE, FAIRVIEW PENNSYLVANIA	
		CN 203386	CN 184931	CHANGE NOTICE	Fractions $\pm 1/64$		Dwn. KAUFFMAN	Description FEED THRU RESIN SEAL FILTER
					Dec. .xx $\pm$		Ckd. 8/27/01	
					Dec. .xxx $\pm$ .010		Apvd.	
					Angles $\pm 0^{\circ} 30'$		Scale NONE	54-790-023
					CODE IDENT. NO. QLSP2			

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Spectrum Control:](#)

[24-0009-2700](#)