


AVERY DENNISON MARKETING SPECIFICATION

HISTORY

| REV. | DATE | DESCRIPTION |
|------|----------|-----------------------|
| C | 04.03.14 | UPDATED TO NEW FORMAT |

THE SUBJECT MATTER DISCLOSED HEREIN EMBODIES PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF THE AVERY DENNISON CO. NONE OF WHICH SHALL BE COPIED, REPRODUCED, DISCLOSED TO OTHERS, PUBLISHED OR USED IN WHOLE OR IN PART, FOR ANY PURPOSE OTHER THAN THAT FOR WHICH IT IS BEING MADE AVAILABLE WITHOUT THE EXPRESS ADVANCE WRITTEN PERMISSION OF A DULY AUTHORIZED AGENT OF THE COMPANY. THIS DOCUMENT IS THE PROPERTY OF THE AVERY DENNISON CO. AND IS TO BE RETURNED TO THE COMPANY ON DEMAND.



| | |
|-----------------------|--|
| MOUNTING: | M8 STUD |
| TENSILE STRENGTH: | 50 LBF / 22.7 KGF MIN. |
| OPERATING TEMP RANGE: | -40°F (-40°C) TO 220°F (105°C) |
| WEIGHT: | 3.37 GRAMS |
| BUNDLE DIAMETER: | Ø 1.6MM TO Ø 44.5MM |
| TOOL: | TOOL, HAND ADJUSTABLE, FOR PLASTIC TIE DOWN STRAP, AVERY DENNISON PART NO. 12001-0 |
| TOOL TENSION SETTING: | 6 - 8 |
| PACKAGING: | 500/BAG, 10 BAGS/MASTER |

APPROVALS: ENG. APPR. *[Signature]* 4/4/14
 Q.A. APPR. *[Signature]* 4/3/2014

AVERY DENNISON
 FASTENER DIVISION
 FITCHBURG, MA 01420 U.S.A.
 TEL. 1-800-225-5913
 FAX. 978-353-6157

| | | |
|---------------------------|--------------|--|
| SPECIFIED TOLERANCES ARE: | | MATERIAL |
| .XX ± .03 INCHES | .X ± .7 MM | NYLON 6/6, IMPACT MODIFIED, HEAT STABILIZED |
| .XXX ± .01 INCHES | .XX ± .25 MM | COLOR |
| ANGULAR: ± 2° | | NATURAL |

| | |
|----------------------------------|------|
| DESCRIPTION | REV. |
| M8 WELD STUD TIE, NATURAL | C |
| STOCK NO. | |
| 20046-0 | |

5 4 3 2 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Avery Dennison:](#)

[20046-0](#)