


AVERY DENNISON MARKETING SPECIFICATION

HISTORY

REV.	DATE	DESCRIPTION
B	10-17-16	UPDATED MODEL

THE SUBJECT MATTER DISCLOSED HEREIN EMBODIES PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF THE AVERY DENNISON CO. NONE OF WHICH SHALL BE COPIED, REPRODUCED, DISCLOSED TO OTHERS, PUBLISHED OR USED IN WHOLE OR IN PART, FOR ANY PURPOSE OTHER THAN THAT FOR WHICH IT IS BEING MADE AVAILABLE WITHOUT THE EXPRESS ADVANCE WRITTEN PERMISSION OF A DULY AUTHORIZED AGENT OF THE COMPANY. THIS DOCUMENT IS THE PROPERTY OF THE AVERY DENNISON CO. AND IS TO BE RETURNED TO THE COMPANY ON DEMAND.



8	△	FLAMMABILITY:	HB RATED PER FMVSS302
9	△	TENSILE STRENGTH:	50 LBF / 222N MIN.
		MOUNTING:	M5/M6 STUDS
		OPERATING TEMP RANGE:	-40°F (-40°C) TO 220°F (105°C)
		WEIGHT:	1.6 GRAMS EACH
		BUNDLE DIAMETER:	\varnothing 1/4" [1.6MM] TO \varnothing 1-3/4" [44.5MM]
		INSTALLATION TOOL:	12001 - HAND TOOL 12500 - PNEUMATIC TOOL
		TOOL TENSION SETTING:	6 - 8
		PACKAGING:	1000/BAG, 5 BAGS/MASTER

△ = INDICATE SPECIAL CHARACTERISTICS

APPROVALS:	ENG. APPR. <i>[Signature]</i> 10/17/16
	Q.A. APPR. <i>[Signature]</i> 10/17/16



FASTENER DIVISION
FITCHBURG, MA 01420 U.S.A.
TEL. 1-800-225-5913
FAX. 978-353-8157

SPECIFIED TOLERANCES	
INCHES	MM
.XX ± .03	.X ± .7
.XXX ± .010	.XX ± .25
ANGULAR: ± 2°	

MATERIAL	NYLON 6/6, IMPACT MODIFIED, HEAT STABILIZED
COLOR	NATURAL

DESCRIPTION	M5/M6 MOUNT 7.5" CABLE TIE	
STOCK NO.	20062-0	REV.
		B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Avery Dennison:](#)

[20062-0](#)