


AVERY DENNISON MARKETING SPECIFICATION

© 2019 AVERY DENNISON CORPORATION. ALL RIGHTS RESERVED


HISTORY

REV.	DATE	DESCRIPTION
A	9/13/19	INITIAL RELEASE



NOTES:

1. Δ = INDICATES SPECIAL CHARACTERISTIC
2. \triangleright ALL PARTS HAVE ONE OF TWO DIFFERENT IDENTIFIERS TO DISTINGUISH FROM SIMILAR SIZE OVAL ARROW TIES.



DETAIL A
SCALE 4 : 1

DETAIL B
SCALE 4 : 1

10	Δ	FLAMMABILITY:	HB RATED PER FMVSS302
11	Δ	TENSILE STRENGTH:	50 lbf / 222N MIN.
		MOUNTING:	6.2mm X 12.2 mm SLOTTED HOLE. 7.0mm X 12.0 mm SLOTTED HOLE. THICKNESS OF 0.6mm TO 3.0mm
		OPERATING TEMP RANGE:	-40 °F (-40 °C) TO 239 °F (115 °C) CONTINUOUS AND 257 °F (125 °C) AT MAXIMUM EXPOSURE
		WEIGHT:	1.9g
		BUNDLE DIAMETER:	\varnothing 1.6mm TO \varnothing 38.0mm
		TOOL:	12001 - HAND TOOL 12500 - PNEUMATIC TOOL
		TOOL TENSION SETTING:	6 - 8
		PACKAGING:	500/BAG, 10 BAGS/MASTER

APPROVALS:

ENG. APPR.	<i>Bert Uschold</i>	9.13.19
Q.A. APPR.	<i>Caitlin Vaillancourt</i>	9.13.19

SPECIFIED TOLERANCES ARE:

.XX \pm .03 INCHES	.X \pm .7 mm
.XXX \pm .010 INCHES	.XX \pm .25 mm
ANGULAR: \pm 2°	

MATERIAL	NYLON 6/6, IMPACT MOD, HEAT STABILIZED
COLOR	BLACK



FASTENER DIVISION
FITCHBURG, MA 01420 U.S.A.
TEL. 1-800-225-5913
FAX. 978-353-8157

DESCRIPTION	OVAL ARROW TIE, 6.2x12.2
STOCK NO.	20179-0
REV.	A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Avery Dennison:](#)

[20179-0](#)