



NOTES:

1. MATES WITH STANDARD ϕ 1/8 PHONO PLUG.
2. SLEEVE TERMINAL, WASHER, AND HEX NUT PACKAGED UNASSEMBLED.
3. MATERIALS
HOUSING - COPPER ALLOY, NICKEL PLATED
INSULATORS - THERMOPLASTIC
TIP TERMINAL - COPPER ALLOY, MATTE TIN PLATED
SLEEVE TERMINAL - COPPER ALLOY, TIN PLATED
WASHER - STEEL, NICKEL PLATED
HEX NUT - COPPER ALLOY, NICKEL PLATED
4. THIS PRODUCT IS RoHS COMPLIANT.

CUSTOMER DRAWING

					THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.				
					SIZE	WIDTH	MULT	LBS/M	TEMPER
					UNLESS OTHERWISE SPECIFIED			FINISH	
					1. ALL DIMENSIONS IN INCHES			MATERIAL	
					- TWO PLACE DECIMALS ±0.02			SPEC No.	
					- THREE PLACE DECIMALS ±0.005			SCALE	
C	27760	8-31-16	TO	TJK	FIRST USED ON			2:1	
B	25504	12/8/06	RS	TJK	DATE DRAWN	BY	CHKD	APVD	
A	26172	10/20/06	RS	TJK	1/5/09	RS	RS	TJK	
REV					ECO NUMBER	DATE	BY	APVD	
REVISIONS					DO NOT SCALE DRAWING				
					NAME			PART No.	
					PHONO JAX, REAR PANEL MOUNT, RoHS			3501FRX	
					SHEET 1 OF 1				
					REV C				

SolidWorks CAD File



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[3501FRX](#)