

**ST-604**  
OVERMOLDED 4 PIN FEMALE TINI-QG


CONTACTS - SPECIAL COPPER ALLOY, SILVER PLATED  
INSULATOR - NATURAL (BROWN) THERMOPLASTIC  
SHELL - COPPER ALLOY, NICKEL PLATED  
OVERMOLD - BLACK THERMOPLASTIC.

**ST-604**  
OVERMOLDED 4 PIN FEMALE TINI-QG


CONTACTS - SPECIAL COPPER ALLOY, SILVER PLATED  
INSULATOR - NATURAL (BROWN) THERMOPLASTIC  
SHELL - COPPER ALLOY, NICKEL PLATED  
OVERMOLD - BLACK THERMOPLASTIC.

Ø0.184  
[4.67]  
4 CONDUCTOR  
FOIL SHIELD  
BLACK PVC

WIRING CHART STRAIGHT THRU WIRING		
ST-604	WIRE COLOR	ST-604
PIN 1	BLACK	PIN 1
PIN 2	WHITE	PIN 2
PIN 3	RED	PIN 3
PIN 4	GREEN	PIN 4
SHELL	SHIELD/ DRAINWIRE	SHELL



**ST-604**  
FRONT MATING VIEW  
BOTH ENDS



NOTES:

- 1. THIS PRODUCT IS RoHS COMPLIANT

**CUSTOMER DRAWING**

					THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.				
					SIZE	WIDTH	MULT	LBS/M	TEMPER
					FINISH			MATERIAL	
					SPEC No.			SPEC No.	
					FIRST USED ON		SCALE		
							1.5:1		
DATE DRAWN		BY	CHKD	APVD					
7/28/20		AB	AB	TJK					
			7/28/20	8/10/20					
REV					NAME			PART No.	
ECO NUMBER					CABLE ASSEMBLY, DOUBLE ENDED 4 PIN FEMALE TINI QG, RoHS			604HH__604X	
DATE									
BY									
APVD									
REVISIONS					DO NOT SCALE DRAWING				
A	28310	08/25/20	PC	TJK					

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[604HH079604X](#)