



NOTES:

1. CABLE RANGE: $\varnothing 0.236-0.354$ [6.0 - 9.0]
2. RECOMMENDED MOUNTING HOLE: $\varnothing 0.656$ [16.67].
3. IP68 RATED WHEN PROPERLY ASSEMBLED. IMMERSED IN 1.8M WATER FOR 24 HOURS.
4. ALL PARTS SHIPPED ASSEMBLED.
5. MATERIALS:
 SEAL NUT, CLAMP NUT, HEX NUT - BLACK, THERMOPLASTIC UL746C (F1) UV RATED
 GASKET AND SEAL RING - BLACK, EDPM RUBBER
6. THIS PRODUCT IS RoHS COMPLIANT.

SECTION A-A
CUSTOMER DRAWING

					THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.							
					SIZE	WIDTH	MULT	LBS/M	TEMPER			
					FINISH			MATERIAL				
					SPEC No.			SPEC No.				
					FIRST USED ON		SCALE 1.5:1					
C	28375	03/30/21	PC	TJK	DATE DRAWN	BY	CHKD	APVD	Switchcraft®			
B	28315	09/09/20	PC	TJK	4/30/20	FM	FM	TJK				
A	28308	07/31/20	PC	TJK	4/30/20	FM	4/30/20	7/2/20				
REV	ECO NUMBER	DATE	BY	APVD	NAME M16 x 1.5 CABLE GLAND, CABLE RANGE $\varnothing 6.0 - 9.0$ mm				PART No.	REV		
REVISIONS					DO NOT SCALE DRAWING					SHEET 1 OF 1	CGM16N35	C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[CGM16N35](#)