



- NOTES:
- PARTS ARE SUPPLIED ON TAPE AND REEL.
REEL SIZE ϕ 13.0 [330] PLASTIC, 100 PARTS PER REEL.
TAPE CONFORMS TO ANSI/EIA-481
 - LIFE TEST: 10,000 CYCLES.
 - MATERIALS:
HOUSING AND CAP - LCP, BLACK
SHELL - STAINLESS STEEL, NICKEL PLATED
CONTACTS - BRASS, GOLD FLASH IN CONTACT AREA, TIN IN SOLDER AREA
 - ELECTRICAL CHARACTERISTICS
CURRENT RATING: 0.5 AMP
VOLTAGE RATING: 40V
 - MECHANICAL CHARACTERISTICS
INSERTION FORCE: 4.5Kgf MAX
WITHDRAWAL FORCE: 1.0~1.4 Kgf (INITIAL)
 - OPERATING TEMPERATURE: -25°C TO +85°C
 - THIS PRODUCT IS RoHS COMPLIANT.

REV	ECO NUMBER	DATE	BY	APVD
B	28443	11/15/21	PC	TJK
A	28330	10/22/20	PC	TJK

REVISIONS

UNLESS OTHERWISE SPECIFIED

1. ALL DIMENSIONS IN INCHES [mm]
- TWO PLACE DECIMALS ± 0.02 [0.5]
- THREE PLACE DECIMALS ± 0.005 [0.13]

DO NOT SCALE DRAWING

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.									
SIZE	WIDTH	MULT	LBS/M	TEMPER					
FINISH SPEC No.		MATERIAL SPEC No.							
FIRST USED ON				SCALE 3.5:1					
DATE DRAWN	BY	CHKD	APVD						
9/4/20	FM	FM	TJK						
			9/4/20	10/5/20					
NAME				PART No.		REV			
HDMI TYPE A, VERTICAL FEMALE, RoHS				RAVHD19TR		B			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[RAVHD19TR](#)