


**STRIPPING DIMENSIONS
FOR 4505R CABLE**



NOTES:

1. MUST BE ROHS COMPLIANT.
2. MUST BE USEABLE TO 12GHZ.
3. ALL DIMENSIONS ARE REF.
4. CRIMP CONTACT PIN WITH 0.042 SQUARE.
5. CRIMP FERRULE WITH 0.255 HEX.

CUSTOMER DRAWING

					THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.					
					SIZE	WIDTH	MULT	LBS/M	TEMPER	
					UNLESS OTHERWISE SPECIFIED			FINISH		
					1. ALL DIMENSIONS IN INCHES [mm]			MATERIAL		
					- TWO PLACE DECIMALS ±0.02 [0.5]			SPEC No.		
					- THREE PLACE DECIMALS ±0.005 [0.13]			SCALE		
					FIRST USED ON *			1:1		
					DATE DRAWN	BY	CHKD	APVD	Switchcraft®	
					10/7/19	SRC	TJK 5/4/20	TJK 5/4/20		
A	28255	2/21/20	TJK	TJK	NAME				SHEET 1 OF 1	
REV	ECO NUMBER	DATE	BY	APVD	PLUG, MICRO BNC FOR 4505R CABLE				PART No.	
REVISIONS					DO NOT SCALE DRAWING				UHDMB05	REV
									A	



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[UHDMB05](#)