



DIMENSIONS SHOWN ARE REFERENCE ONLY

NOTES:

1. MEETS SMPTE 2082-1
CHARACTERISTIC IMPEDANCE :75 OHMS
CONTACT RESISTANCE: 50 MILLIOHMS MAX.
2. WIRING: CENTER CONTACT TO CENTER CONTACTS
GROUND SLEEVE TO GROUND SLEEVE
3. MATERIAL:
PLUG: COPPER ALLOY, NICKEL PLATED.
CONTACT: COPPER ALLOY, GOLD PLATED.
INSULATOR: TEFLON
CABLE: SILVER PLATED CONDUCTOR, COPPER/TIN SHIELD.
OVERMOLD: THERMOPLASTIC ELASTOMER
4. THIS PRODUCT IS RoHS COMPLIANT.

CUSTOMER DRAWING

					THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.				
					SIZE	WIDTH	MULT	LBS/M	TEMPER
					FINISH			MATERIAL	
					SPEC No.			SPEC No.	
					FIRST USED ON		SCALE		
							3:2		
DATE DRAWN		BY	CHKD	APVD					
5/01/17		PNK	PNK	SRC					
			5/01/17	5/01/17					
					NAME			PART No.	
					LOOPING PLUG			VMMLPUHD	
					UHD MICRO, OVERMOLDED, RoHS			REV	
								0A	

					UNLESS OTHERWISE SPECIFIED				
					1. ALL DIMENSIONS IN INCHES [mm]				
					- TWO PLACE DECIMALS ±0.02 [0.5]				
					- THREE PLACE DECIMALS ±0.005 [0.13]				
0A	PDR 16006	5/01/17	PNK	SRC					
REV	ECO NUMBER	DATE	BY	APVD					
					REVISIONS				

DO NOT SCALE DRAWING

SolidWorks CAD File

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[VMMLPUHD](#)