

Specification

Part No.	: PC27.07.0100A
Product Name	: TheStripe™ 850 / 900 / 1800 / 1900 MHz GSM PCB Antenna W/100mm IPEX 1.13mm Diameter MHF I Connector
Feature	: 34mm*7mm*0.8mm 850 / 900 / 1800 / 1900MHz GSM Compatible with Hirose U.FL RoHS Compliant



1. Introduction


This miniaturized low profile PCB antenna is based on smart TheStripe™ antenna technology. It consists of a PCB antenna and 1.13mm co-axial cable with IPEX MHFI (U.FL) connector.

2. Specification


ELECTRICAL				
Frequency (MHz)	824 ~ 896	880~960	1710~1880	1850~1990
Free Space Peak Gain	-4.1dBi	-13dBi	0.6dBi	-0.4dBi
Free Space Efficiency	13%	8%	51%	11%
Impedance	50Ω			
Polarization	Linear			
Radiation Pattern	Omni			
MECHANICAL				
Antenna Dimensions	34 x 7 x 0.8mm			
Cable	1.13 co-axial			
Connector	IPEX MHF I			
ENVIRONMENTAL				
Operation Temperature	-40°C to 85°C			
Humidity	Non-condensing 65°C 95% RH			

3. S11 Property


3.1. Return Loss




3.2. VSWR




3.3. Efficiency



3.4. Peak Gain




3.5. Average Gain




4. Antenna Radiation Pattern

4.1. Radiation Pattern in Free Space

4.1.1. E-plane Radiation




4.1.2. H-plane Radiation




4.2. Radiation Pattern on ABS


4.2.1. E-plane Radiation



4.2.2. H-plane Radiation



5. Drawing




	Name	Material	Finish	QTY
1	PC27 PCB	FR4.08t	Black	1
2	1.13 Coaxial Cable	FEP	Black	1
3	IPEX MHF1	Brass	Gold	1


All material must be RoHS compliant.
 Open/Short QC, VSWR required.

6. Packaging


100pc PC27.09.0100A per PE Bag
Bag Dimensions - 285 x 160mm
Weight - 240g




500pcs PC27.07.0100A per PE Large Bag
Bag Dimensions - 450 x 280mm
Weight - 1.2kg



2000 pcs PC27.07.0100A per carton
Carton - 320 x 250 x 230mm
Weight - 4.8Kg



Pallet Dimensions 1200x 1000 x 1350mm
60 Cartons per Pallet
12 Cartons per layer
5 Layers



Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein.

Reproduction, use or disclosure to third parties without express permission is strictly prohibited.

Copyright © Taoglas Ltd.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Taoglas:](#)

[PC27.07.0100A](#)