




APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	01/17/07	
A		REVISED COLOR	5/11/09	



RECOMMENDED PCB LAYOUT

SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Ivory

Contacts: Brass

Plating:

Tin over Nickel underplate overall

Electrical:

Operating voltage: 250 VAC max

Current rating: 1 Amps max

Contact resistance: 20 mohms max

Insulation resistance: 100 Mohms min

Dielectric withstanding voltage: 250 VAC for 1 minute

Temperature Rating:

Operating temperature: -40°C to +85°C

Environmental:

Lead free, RoHS compliant.



A=.049 [1.25] X NO. OF SPACES
B=.049 [1.25] X NO. OF SPACES X+.070 [1.80]
C=.049 [1.25] X NO. OF SPACES X+.118 [3.00]
D=.049 [1.25] X NO. OF SPACES X+.259 [6.60]

ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

MX 1.25mm WAFER 180° SMT

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				TITLE			
INCHES				Holes			
.X	± .10	ØX	± .10	.X	± .10	ØX	± .10
.XX	± .020	ØXX	± .015	.XX	± .020	ØXX	± .015
.XXX	± .015	ØXXX	± .010	.XXX	± .015	ØXXX	± .010
APPROVALS				DATE			
DRAWN	BW		01/17/07	SIZE	PART NO.	REV.	
CHECKED				X	125SH-B-XX-TS-SMT	A	
APPROVED				REF:	SCALE: NTS	SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[125SH-B-07-TS-SMT](#) [125SH-B-06-TS-SMT](#) [125SH-B-03-TS-SMT](#) [125SH-B-08-TS-SMT](#) [125SH-B-05-TS-SMT](#)
[125SH-B-10-TS-SMT](#) [125SH-B-02-TS-SMT](#) [125SH-B-15-TS-SMT](#) [125SH-B-12-TS-SMT](#) [125SH-B-09-TS-SMT](#)
[125SH-B-04-TS-SMT](#) [125SH-B-13-TS-SMT](#) [125SH-B-11-TS-SMT](#) [125SH-B-14-TS-SMT](#)