





Rev	AWO #	Description	Date	Appr
-		RELEASED	01/17/07	

APPROVED: _____
 DATE: _____ TITLE: _____



SPECIFICATIONS:

- Material: Phosphor Bronze
- Contact: Tin over Copper underplate overall
- Plating: Tin over Copper underplate overall
- Electrical:
 - Operating voltage: 50 VAC max
 - Current rating: 1 Amp max
 - Insulation resistance: 500 Mohms min @ 500 VDC
 - Dielectric withstanding voltage: 500 VAC for 1 minute
 - Contact resistance: 20 mohms max.
- Mechanical:
 - Recommended Wire Awg: 28 - 32 Awg
 - Temperature Rating: Operating temperature: -25°C to +85°C
 - Environmental: Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED

INCHES	HOLDS
.X ± .10	ØX ± .10
.XX ± .020	ØXX ± .015
.XXX ± .015	ØXXX ± .010

APPROVALS

DATE	DATE

ADAM TECH
 909 Railway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE: SH1.0mm TERMINAL

DRAWN	BW	01/17/07
CHECKED		
APPROVED		

SIZE	PART NO.	REV.
X	1CTA-R	-
REF:	SCALE: NTS	SHEET 1 OF 1

6 5 4 3 2 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[1CTA-R](#)