





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/22/08	
A		REDRAWN	10/17/11	
B		ADDED DIM.	10/21/20	AY/NP



Positions: 2, 4, 6, 8, 10, 12, 14, 16, 18, 20, 22, 24
A = .165 [4.20] X No. of Spaces per row
B = .165 [4.20] X No. of Positions per row + .055 [1.40]

SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: Natural

Electrical:

Operating voltage: 600 VAC max

Current rating: / Circuit (See Chart)

Insulation resistance: 1000 Mohms min @ 500 VDC

Dielectric withstanding voltage: 1500 VAC for 1 minute

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant.

WIRE SIZE	CIRCUITS			
AWG	2	4~6	8~10	12~24
18	9 A	8 A	7 A	6 A
20	7 A	6 A	5 A	5 A
22	5 A	4 A	4 A	4 A
24	4 A	3 A	3 A	3 A



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES

.X ±.10 Ø.X ±.10
.XX ±.020 Ø.XX ±.015
.XXX ±.015 Ø.XXX ±.010

APPROVALS		DATE
DRAWN	DY	9/22/08
CHECKED		
APPROVED		

**ADAM
TECH**

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
WIRE TO WIRE CONNECTOR HOUSING
FEMALE, 4.2MM PITCH

SIZE X	PART NO. DMH-XX-V0	REV. B
REF: S00123T	SCALE: NTS	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[DMH-08-V0](#) [DMH-04-V0](#) [DMH-06-V0](#) [DMH-10-V0](#)