





Rev	AWO #	Description	Date	Appr
-		RELEASED	1/28/05	

APPROVED: \_\_\_\_\_  
 DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_



PCB LAYOUT



**SPECIFICATIONS:**

- Material: Insulator: PBT, Glass reinforced, rated UL 94V-0
- Insulator color: Black
- Contacts: Phosphor Bronze
- Plating: Tin over Copper underplate overall
- Electrical: Operating voltage: 250 VAC max
- Current rating: 1 Amp max
- Contact resistance: 20 mohms max initial
- Insulation resistance: 5,000 Mohms min
- Dielectric withstanding voltage: 1,000 VAC for 1 minute
- Temperature Rating: Operating temperature: -55°C to +105°C
- Environmental: Lead free, RoHS compliant

Positions: 6, 8, 14, 16, 18, 20, 22, 24, 28, & 32  
 A = .100 [2.54] x No. of Positions Per Row  
 B = .100 [2.54] x No. of Spaces Per Row

**ADAM TECH**

909 Railway Avenue, Union, NJ 07083  
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE: IC SOCKET, .300" ROW SPACING  
 TIN PLATED

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE IN INCHES [MM]		TOLERANCES: EXCEPT AS NOTED	
INCHES	HOLES	INCHES	HOLES
.X ± .10	ØX ± .10	.XX ± .020	ØXXX ± .015
.XXX ± .015	ØXXX ± .010		
APPROVALS		DATE	
DRAWN	SS	1/28/05	
CHECKED			
APPROVED			
SIZE	PART NO.	SCALE:	REV.
X	ICS-3XX-T	MKS	
REF:		SHEET	1 OF 1



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[ICS-324-T](#) [ICS-328-T](#) [ICS-316-T](#) [ICS-308-T](#) [ICS-318-T](#) [ICS-314-T](#) [ICS-320-T](#) [ICS-306-T](#)