


APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/26/18	



Poles: 01 thru 15

SPECIFICATIONS:

Material:

Insulator: PBT, rated UL 94V-0

Insulator color: Black

Contacts: Copper Alloy, Tin plated

Screw: M6 Steel, Zinc plated

Electrical:

Voltage rating: 600 V

Current rating: 115 A

Contact resistance: 20 mohms

Insulation resistance: 1000 Mohms / DC500V

Dielectric withstanding voltage: 2,500 VAC for 1 minute

Mechanical:

Wire Range: 8~2 AWG

Torque: 3.0Nm

Temperature Rating:

-40°C to +130°C

Environmental:

Lead free, RoHS compliant.



	linear dimension(Tolerances Standard)											≡	—	□	//	⊥
	to	over 6 to 10	over 10 to 18	over 18 to 30	over 30 to 50	over 50 to 80	over 80 to 120	over 120 to 160	over 160 to 200	over 200 to 250	over 250 to	all	to 5	over 5 to 30	over 30 to 120	over 120 to
variable range	to 6	to 10	to 18	to 30	to 50	to 80	to 120	to 160	to 200	to 250	to	all	to 5	over 5 to 30	over 30 to 120	over 120 to
tolerance	±0.1	±0.14	±0.19	±0.25	±0.32	±0.43	±0.57	±0.72	±0.88	±1.05	±1.25	0.5	0.025	0.06	0.12	0.4

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MILLIMETERS
TOLERANCES: EXCEPT AS NOTED

SEE CHART

APPROVALS		DATE
DRAWN	AY	11/26/18
CHECKED	AC	11/26/18
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
TERMINAL BLOCK, .827 [21.00] PITCH
W/ CLEAR COVER

SIZE X	PART NO. TBU-XX-W4-CCS	REV. -
REF: S00067C	SCALE: NTS	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[TBU-05-W4-CCS](#) [TBU-03-W4-CCS](#) [TBU-06-W4-CCS](#) [TBU-04-W4-CCS](#) [TBU-02-W4-CCS](#)