





APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	6/8/05	
A		REDRAWN	4/19/13	



SPECIFICATIONS:

Material:
 Insulator: PBT, glass reinforced, rated UL 94V-0
 Insulator color: Black
 Cover: PBT, glass reinforced, rated UL 94V-0, Color: Black
 Contacts: Phosphor Bronze
 Shell: Brass, Tin plated
 Spring Chip: Brass, Tin plated
 Rear Shell: SPCC, Nickel plated
Plating:
 Gold flash over Nickel underplate on contact area,
 Tin over copper underplate on solder tails.
Electrical:
 Operating voltage: 250 VAC max.
 Current rating: 1.5 Amp max.
 Contact resistance: 30 mohms max.
 Insulation resistance: 1000 Mohms min.
 Dielectric withstanding voltage: 750 VAC for 1 minute
Environmental:
 Lead free, RoHS compliant.



ADAM TECH

909 Railway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE: UNIVERSAL SERIAL BUS, A TYPE
 QUAD PORT, RIGHT ANGLE

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]	
TOLERANCES: EXCEPT AS NOTED	
INCHES	HOLES
.X ± .10	± .10
.XX ± .020	± .015
.XXX ± .015	± .010
APPROVALS	DATE
DRAWN	SS
CHECKED	6/8/05
APPROVED	

SIZE	PART NO.	REV.
X	USB-A-Q-RA	A
REF:	S00095T	SHEET 1 OF 1
SCALE:	NTS	



6 5 4 3 2 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[USB-A-Q-RA](#)