

## 16-Port Fiber Patch Panel, 1U (SC/SC), Multimode or Singlemode

MODEL NUMBER: N490-016-SCSC



### Highlights

- Simplified Fiber Optic Patching
- Multimode 62.5/125, 50/125, and Singlemode 9/125
- 16 ports in 1U of rackspace

### Package Includes

- 16 Port SC/SC Duplex Multimode / Singlemode Fiber Optic Patch Panel

### Description

This 16-port 1U rack-mount SC/SC Fiber Optic Patch Panel provides efficient and easy management of fiber optic cables in the rack or cabinet. Pre-loaded, feed-thru duplex multimode connectors are mounted on a 16-gauge, cold rolled, black powder coated steel panel. Use with 62.5/125 or 50/125 multimode fiber Ethernet cables, as well as 9/125 Singlemode. Panel measures 19 inches wide by 1.75 inches high.

### Features

- 16 ports SC/SC
- Only 1U of rack-space
- Use with 62.5/125 or 50/125 Multimode fiber patch cables, and 9/125 Singlemode
- Available in ST/ST, SC/SC, LC/LC,

## Specifications

OVERVIEW	
UPC Code	037332135322
Product Type	Feed-Through
Technology	Multimode
PHYSICAL	
Shipping Dimensions (hwd / in.)	4.00 x 3.00 x 21.70
Shipping Dimensions (hwd / cm)	10.16 x 7.62 x 55.12
Shipping Weight (lbs.)	1.30
Shipping Weight (kg)	0.59

CONNECTIONS	
Number of Ports	16
Side A - Connector 1	SC DUPLEX (FEMALE)
Side B - Connector 1	SC DUPLEX (FEMALE)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[N490-016-SCSC](#)