

25U SmartRack 2-Post Open Frame Rack - Organize and Secure Network Rack Equipment

MODEL NUMBER: SR2POST25



Description

Tripp Lite's SR2POST25 2-Post SmartRack Open Frame Rack is an economical way to accommodate 25U of rack space for 19-inch rackmount applications in limited spaces that do not require a lockable enclosure. Its heavy-duty, aluminum construction can safely support 800 lbs (362.9 kgs) of rackmount equipment, and its open design provides easy access to equipment and cabling. The black, textured powder coat finish makes it resistant to scratching while giving it a "classic," attractive appearance. The SR2POST25 is easy to install due to a self-squaring design combined with 12-24 threaded and numbered mounting positions, and bolt down provisions. It uses toolless button-hole mounting for vertical PDUs and cable managers. In high-density environments, multiple units can be bolted together side by side for easy expansion or customization. The SR2POST25 2-Post SmartRack Open Frame Rack has been approved by EIA-310-D, IEC 60297-3-100, and RoHS, and is backed by a 5-year warranty.

Features

- Supports 800 lbs (362.9 kgs) of rackmount equipment
- Textured powder coat finish
- Heavy Duty Aluminum construction
- 12-24 threaded and numbered mounting positions
- Toolless button holes to accept PDUs or cable managers
- Bolt down provisions
- Self squaring design
- Black finish
- Easy assembly

Specifications

Highlights

- 25U 2-post open frame rack
- Black aluminum with 12-24 threaded and numbered mounting holes
- Toolless button holes to accept PDUs or cable managers

Package Includes

- SR2POST25
- 28 pieces each of 12-24 screws and washers for equipment mounting
- Installation hardware
- Cable management hooks
- Warranty Information
- Owner's Manual



OVERVIEW	
UPC Code	037332143143
Device Compatibility	Patch Panel; Network Switch; UPS; Server
Rack Type	Open-Frame
PHYSICAL	
Color	Black
EIA Mounting Rails	12-24 threaded and numbered mounting positions
Maximum Device Depth (cm)	121.92
Maximum Device Depth (in.)	48
Maximum Device Depth (mm)	1,219
Rack Height	25U
Shipping Dimensions (hwd / cm)	11.43 x 15.24 x 133.60
Shipping Dimensions (hwd / in.)	4.50 x 6.00 x 52.60
Shipping Weight (kg)	11.79
Shipping Weight (lbs.)	26.00
Unit Dimensions (hwd / cm)	124.46 x 51.56 x 12.06
Unit Dimensions (hwd / in.)	49 x 20.3 x 4.75
Unit Weight (kg)	10.43
Unit Weight (lbs.)	23
Weight Capacity - Stationary (kg)	363
Weight Capacity - Stationary (lbs.)	800
Rack Depth	Extra Deep
Number of Vertical Mounting Rails	2
STANDARDS & COMPLIANCE	
Approvals	EIA-310-D, IEC 60297-3-100, RoHS
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SR2POST25](#)