


MTP/MPO (APC) Singlemode Slim Trunk Cable, 24-Strand, 40/100 GbE, 40/100GBASE-PLR4, Plenum, 6mm Dual Jacket, 45 m (147 ft.)

MODEL NUMBER: N392-45M-3X8-AP



Highlights

- Push/pull tab connectors easily install/remove with one hand
- Factory-terminated 8-fiber MTP/MPO connectors
- Angled APC connectors protect laser against destabilization
- 100% tested for low insertion loss and back reflection
- Yellow color for easy singlemode identification

Package Includes

- N392-45M-3X8-AP MTP/MPO Singlemode Slim Trunk Cable, Yellow, 45 m

Premium 8.3/125 singlemode fiber optic cabling for transmitting 40/100 Gb data and voice signals. Designed for high-density connections between network equipment in telecom rooms and data centers.

Description

The N392-45M-3X8-AP MTP/MPO (APC) Singlemode Slim Trunk Cable (3xF/3xF) supports 40/100 Gb Ethernet speeds and is designed for high-density connections between network equipment in telecommunication rooms and data centers. With three female MTP/MPO connectors on each end, this singlemode fiber optic cable is recommended for high-density fiber patching between data center MDFs (main distribution frames) and IDFs (intermediate distribution frames).

The factory-terminated 8-fiber MTP/MPO connectors are about the same size as SC connectors, but are 12 times denser, freeing up rack space for other cables. The APC connectors are angled to prevent infrared light entering the fiber from bouncing back into the laser. Optimized for QSFP+ 40GBASE-PLR4 and QSFP28 100GBASE-PSM4 networks, this cable is tested for low insertion loss and back reflection on every connector and attenuation loss that meets or exceeds current standards.

The N392-45M-3X8-AP is colored yellow for instant identification in a crowded switch or patch panel as a singlemode cable. Push/pull tab connectors are easily accessible in high-density data center applications and make the plug-and-play cable easy to install and remove with one hand. The 6-millimeter dual plenum-rated jacket and bend-insensitive fiber are perfect for connecting high-speed network components in ceilings, walls and ducts.

Features

8.3/125 Rated Singlemode Cable for 40/100 Gb Ethernet Applications

- Designed to extend high-density connections between network equipment in telecom rooms and data centers



- Recommended for patching between data center MDFs and IDF's
- Optimized for QSFP+ 40GBASE-PLR4 and QSFP28 100GBASE-PSM4 networks
- 6 mm dual plenum-rated jacket and bend-insensitive fiber perfect for ceilings, walls and ducts
- Yellow-colored for identification as a singlemode cable

Factory-Terminated MTP/MPO APC Connectors with Push/Pull Tabs

- 8-fiber female connectors 12 times denser than SC connectors
- Push/pull tab connectors easy to install and remove with one hand
- Angled connectors prevent light from reflecting back into laser
- 100% tested for low insertion loss and back reflection

Specifications

OVERVIEW	
UPC Code	037332205483
Technology	MTP/MPO; Singlemode
INPUT	
Cable Length (ft.)	147.6
Cable Length (m)	45
PHYSICAL	
Shipping Dimensions (hwd / in.)	4.720 x 10.240 x 10.240
Shipping Dimensions (hwd / cm)	11.99 x 26.01 x 26.01
Shipping Weight (lbs.)	4.1900
Shipping Weight (kg)	1.90
Color	Yellow
ENVIRONMENTAL	
Operating Temperature Range	-4 TO 140 F (-20 TO 60 C)
Storage Temperature Range	-4 TO 140 F (-20 TO 60 C)
COMMUNICATIONS	
Network Speed	10Gbps / 40Gbps / 100Gbps
CONNECTIONS	
Side A - Connector 1	(3) 8-STRAND MTP (FEMALE)
Side B - Connector 1	(3) 8-STRAND MTP (FEMALE)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[N392-45M-3X8-AP](#)