

4U ABS Server Rack Equipment Shipping Case

MODEL NUMBER: SRCASE4U



4U server case lets you safely transport sensitive rack-mount equipment to trade shows, aboard airplanes or between facilities.

Features

4U Server Rack Case Lets You Safely Transport Rack-Mount Equipment This SmartRack® 4U server case houses EIA-standard 19-inch rack equipment while it's being moved from one location to another. Constructed from heavy-duty ABS, the SRCASE4U features four stationary mounting rails that support up to 4U of servers, switches, patch panels, UPS systems and other rack components up to 20.5 inches deep. Maximum load capacity is 75 lbs (34 kgs). The case is ideal for transporting sensitive rack equipment to trade shows or other facilities without fear of damage.

Protects Sensitive Devices against Moisture, Debris, Bumps and Jolts This server rack case comes fully assembled with a built-in handle on each side for convenient transportation. Once the device is mounted inside using the included hardware, both the front and rear covers with rubber gaskets are latched securely to keep out moisture, dust and other damaging elements. A zippered pouch inside one cover stores extra hardware or other accessories. The SRCASE4U stacks securely with other identical cases.

Highlights

- Fully assembled 4U ABS rack case for transporting equipment between facilities
- Stationary mounting rails allow secure installation using included hardware
- Latching front and rear covers designed to keep out moisture, dust and debris
- Interior zippered pouch allows storage of extra hardware and other accessories
- Mounts 4U of EIA-standard 19 in. rack equipment up to 20.5 in. deep and 75 lbs (34 kgs)

Applications

- Safely transport 4U of rack-mount equipment to a trade show or a different facility
- Carry rack-mount DJ equipment, amplifiers and other professional audio gear to music venues

Package Includes

- SRCASE4U 4U ABS Server Rack Equipment Flight Case
- (8) M5 screws
- (8) M5 cup washers

Specifications

OVERVIEW	
UPC Code	037332210340
Rack Type	Enclosure
PHYSICAL	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Color	Black
Maximum Device Depth (cm)	52.07
Maximum Device Depth (in.)	20.5
Maximum Device Depth (mm)	521
Rack Height	4U
Shipping Dimensions (hwd / cm)	26.01 x 56.01 x 57.99
Shipping Dimensions (hwd / in.)	10.24 x 22.05 x 22.83
Shipping Weight (kg)	6.35
Shipping Weight (lbs.)	14.00
Unit Dimensions (hwd / cm)	22.86 x 50.8 x 54.86
Unit Dimensions (hwd / in.)	9 x 20 x 21.6
Unit Weight (kg)	5.60
Unit Weight (lbs.)	12.34
Weight Capacity - Stationary (kg)	34
Weight Capacity - Stationary (lbs.)	75
STANDARDS & COMPLIANCE	
Certifications	EIA-310-E
Approvals	REACH
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SRCASE4U](#)