

5-Port USB Charging Station with Built-In Device Storage, 12V 4A (48W) USB Charger Output

MODEL NUMBER: U280-005-ST



Charges and organizes up to 5 electronic devices at the same time. Storage compartment neatly organizes your excess cabling to reduce clutter when charging, and stores it out of the way when not in use. Recommended for quick-charging and storing tablets, smartphones and other mobile devices.

Description

Whether you're at home or in the office, Tripp Lite's U280-005-ST 5-Port USB Charging Station provides enough ports and power to keep your devices at 100% capacity. No more peering behind furniture to find an available outlet or unplugging one device to charge another. You can charge up to five tablets, smartphones and other devices at the same time. The U280-005-ST doesn't require a computer, so you can take it anywhere AC power is available.

The U280-005-ST features five USB-A ports, each capable of delivering up to 5V, 2.4A, which is enough for charging even battery-intensive devices like the Apple® iPad®. In addition, this charging station doubles as a storage unit by providing space to neatly organize cabling while your devices charge. When not in use, cables can be stored in the compartment and kept out of the way. The included adjustable brackets accommodate the number and size of the devices being charged.

To charge your USB devices, simply connect the five-foot power cord's NEMA 1-15P plug to an AC power outlet, and connect your devices to the available USB ports. The unit protects against overheating, overcurrent and overcharging—in fact, it stops charging as soon as your devices' batteries are at full capacity. Also, each port complies with USB Battery Charging (BC) specification v1.2. The brackets and power supply store conveniently in the charging station when not in use.

Features

Charges Up to 5 Devices at the Same Time Recommended for charging tablets, smartphones and other devices at home or work Functions anywhere AC power is available—no computer required

Provides Plenty of Juice for Charging Delivers up to 5V, 2.4A per port—enough for charging battery-intensive devices like the Apple iPad Protects against overheating, overcurrent and overcharging Complies with USB Battery Charging (BC) specification v1.2

Efficiently Stores Your Cables / Devices Too 7 adjustable brackets provide space to neatly organize devices as they charge Convenient storage compartment lets you neatly organize your cabling while your devices charge When not in use, cables can be stored in the compartment and kept out of the way

Easy to Use External dual-voltage power supply with C8 power inlet and detachable C7 to 1-15P 5 ft. cord No computer required

Highlights

- 5V, 2.4A per port for charging battery-intensive devices
- All five ports support USB Battery Charging (BC) specification v1.2
- 7 adjustable storage brackets for organizing devices
- Storage compartment neatly organizes your cabling
- External dual-voltage power supply with NEMA 1-15P plug
- Protects against overheating, overcurrent and overcharging

Package Includes

- U280-005-ST 5-Port USB Charging Station
- (7) Storage brackets
- External power supply (Input: 100–240V, 50/60 Hz, 1.5A; Output: 12V, 4A)
- C7 to NEMA 1-15P power cord, 5 ft.
- Quick Start Guide



Specifications

OVERVIEW	
UPC Code	037332199584
Product Type	Charging Station
Charging Form Factor	Charging Hub
AC Adapter	Input: 100-240V, 50/60Hz, 1.5A; Output: 12V, 4A
Device Compatibility	Phone; Tablet; Amazon Kindle
Technology	USB
INPUT	
Nominal Input Voltage(s) Supported	120V AC; 230V AC
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
Input Plug Type	NEMA 1-15P (NON-POLARIZED)
External Power Supply Plug(s)	NEMA 1-15P North America
OUTPUT	
Output Capacity	12V 4A
Overload Protection	Yes
POWER	
External Power Supply Input Specs (V / Hz / A)	100-240V / 50/60Hz / 1.5A
External Power Supply Output Specs (V / A)	12V / 4A
External Power Supply Cord Length (m.)	1
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.5 x 10mm, Positive Pin, Negative Sleeve
External Power Supply Certifications	CCC; FCC; GS; PSE; RoHS; TUV; UL; cUL
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Blue (Power)
CHARGING	
Charging Ports / Amps	(5) 2.4A
Number of Charging Ports	5
Total Charging Amps	4A
Charging Method	USB



Total Charging Watts	48
Charging Ports Detail	USB-A: 12V/4A
Charging Port Type	(5) USB A (FEMALE)
Charging Method Detail	5V - 1.5A (7W)
PHYSICAL	
Color	Black
Material of Construction	Polycarbonate
Shipping Dimensions (hwd / cm)	6.86 x 15.24 x 25.65
Shipping Dimensions (hwd / in.)	2.70 x 6.00 x 10.10
Shipping Weight (kg)	0.93
Shipping Weight (lbs.)	2.05
Unit Dimensions (hwd / cm)	2 x 16.8 x 12.4
Unit Dimensions (hwd / in.)	0.79 x 6.6 x 4.9
Unit Packaging Type	Box
Unit Weight (kg)	0.59
Unit Weight (lbs.)	1.3
ENVIRONMENTAL	
Operating Temperature Range	41 to 95 F (5 to 35 C)
Storage Temperature Range	-4 to 122 F (-20 to 50 C)
Relative Humidity	20% to 80% RH, Non-Condensing
Power Consumption (Watts)	12.7
CONNECTIONS	
Ports	5
Side A - Connector 1	NEMA 1-15P (NON-POLARIZED)
Side B - Connector 1	(5) USB A (FEMALE)
SPECIAL FEATURES	
Overcurrent Protection	Yes
Overvoltage Protection	Yes
GaN Technology	No
STANDARDS & COMPLIANCE	
Certifications	Tested to FCC, RoHS, REACH



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U280-005-ST](#)