




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

| LOC | | DIST | | REVISIONS | | | |
|-----|-----|-------------|--|-----------|-----|------|--|
| P | LTR | DESCRIPTION | | DATE | DWN | APVD | |
| | A | WR-08-38 | | 12AUG2008 | KW | CC | |

POSITION 1
IDENTIFICATION FEATURE

1 MATERIAL: HOUSING: NYLON, UL94V-2, BLUE
CONTACTS: BRASS, TIN-PLATED




| | | | |
|-----|----------------------|-------------|-------------|
| 24 | 46.2±0.25 [1.82±.01] | 51.6 [2.03] | 2-2029139-4 |
| 22 | 42.0±0.25 [1.65±.01] | 47.4 [1.87] | 2-2029139-2 |
| 20 | 37.8±0.25 [1.49±.01] | 43.2 [1.70] | 2-2029139-0 |
| 18 | 33.6±0.25 [1.32±.01] | 39.0 [1.54] | 1-2029139-8 |
| 16 | 29.4±0.25 [1.16±.01] | 34.8 [1.37] | 1-2029139-6 |
| 14 | 25.2±0.25 [.99±.01] | 30.6 [1.21] | 1-2029139-4 |
| 12 | 21.0±0.25 [.83±.01] | 26.4 [1.04] | 1-2029139-2 |
| 10 | 16.8±0.13 [.66±.005] | 22.2 [.87] | 1-2029139-0 |
| 8 | 12.6±0.13 [.50±.005] | 18.0 [.71] | 2029139-8 |
| 6 | 8.4±0.13 [.33±.005] | 13.8 [.54] | 2029139-6 |
| 4 | 4.2±0.13 [.17±.005] | 9.6 [.38] | 2029139-4 |
| 2 | - | 5.4 [.21] | 2029139-2 |
| POS | A | B±0.25[.01] | PART NUMBER |

2-2029139-4 SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.

| | |
|---------------------------------|--|
| DWN K. WHITAKER 12AUG2008 | Tyco Electronics Corporation Harrisburg, PA 17105-3608 |
| CHK C. CASH 12AUG2008 | |
| APVD C. CASH 12AUG2008 | |
| PRODUCT SPEC | |
| APPLICATION SPEC | NAME VERTICAL HEADER, BLUE, WITHOUT PEGS, WITH DRAIN HOLES, VAL-U-LOK(TM) |
| WEIGHT | SIZE A2 |
| CUSTOMER DRAWING | CAGE CODE 00779 |
| | DRAWING NO C=2029139 |
| | RESTRICTED TO - |
| | SCALE 5:1 |
| | SHEET 1 of 1 |
| | REV A |



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2029139-6](#)