



LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00	A	CONCEPT	08DEC2008	MS MP



- △ MATERIALS:**  
 HOUSING: HIGH TEMP THERMOPLASTIC, UL94V-0, GRAY.  
 SIGNAL CONTACTS: COPPER ALLOY  
 POWER CONTACTS: COPPER ALLOY
- △ CONTACT FINISH:**  
 ALL OVER: 0.00127 MIN NICKEL  
 COMPLIANT PIN AREA: 0.00127 MIN TIN  
 MATING AREA: 0.00076 MIN GOLD
- △ POSITIONS 1-4 ARE UNPOPULATED AND RESERVED FOR FUTURE USE.**
- △ HOLES INDICATED ARE NOT REQUIRED FOR TYCO PRODUCT.**
- △ TYCO PART NUMBER (XXXXXX-X) AND DATE CODE (YYWW) LOCATED ON SURFACE INDICATED.**
- △ DATUM AND BASIC DIMENSION TO BE ESTABLISHED BY CUSTOMER.**
- △ CONTACT FINISH:**  
 ALL OVER: 0.00127 MIN NICKEL  
 COMPLIANT PIN AREA: 0.00127 MIN TIN-LEAD  
 MATING AREA: 0.00076 MIN GOLD
8. CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT. TECHNICAL REFERENCE: GR-1217-COR, ISSUE 1, NOVEMBER 1995.
9. THIS DRAWING IS RESTRICTED TO HUAWEI CORPORATION

SEQUENCING TABLE	
CONTACT POSN	PIN LENGTH
1-4	NOT USED
5-24	6.1
25, 26, 28-31	14.3
27, 32	4.58
33	11.3
34	8.8

△	Ø	QTY	SIZE NO	PART NO
△	0.762	22	22	2085066-2
△	1.58	8	16	2085066-1
△	0.762	22	22	2085066-1
△	1.58	8	16	2085066-1

DIMENSIONS: mm TOLERANCES UNLESS OTHERWISE SPECIFIED: 9 PLC ±0.5 1 PLC ±0.13 5 PLC ±0.013 4 PLC ±0.001 ANGLES ±0.001		DWN M. SYKES 08DEC2008 CHK M. PERCHERKE 08DEC2008 APVD M. PERCHERKE 08DEC2008		Tyco Electronics Harrisburg, PA 17105-3608	
MATERIAL: PLATING		PRODUCT SPEC: 108-2216 APPLICATION SPEC: 114-13156		NAME: ASSEMBLY, RT ANGLE AdvancedTCA	
FINISH: △ 2 △ 7		WEIGHT: -		SIZE: A   00779   C=2085066 RESTRICTED TO: HUAW	
RESTRICTED CUSTOMER		SCALE: 6:1		SHEET 1 OF 2 REV A	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2085066-1](#)