

SPECIFICATION CONTROL DRAWING

44B4821

TITLE	TWO CONDUCTOR CABLE, JACKETED, 600 VOLT	Date	4-2-07	Revision	C
This specification sheet forms a part of the latest issue of Raychem Specification 55A.					

COMPONENT WIRES - 44A0811

JACKET - RADIATION-CROSSLINKED, MODIFIED ETFE



CABLE CONSTRUCTION DETAILS

PART NUMBER 1/	CONDUCTOR SIZE (AWG)	JACKET THICKNESS (in.)		OUTSIDE DIAMETER (in.)		MAXIMUM WEIGHT (lbs/1000 ft.)
		MINIMUM	NOMINAL	NOMINAL	MAXIMUM	
44B4821-24-*	24	.006	.008	.124	.130	8.1
44B4821-22-*	22	.006	.008	.140	.147	10.9
44B4821-20-*	20	.006	.008	.156	.164	14.5
44B4821-18-*	18	.006	.008	.176	.185	20.1
44B4821-16-*	16	.006	.008	.194	.204	24.8
44B4821-14-*	14	.007	.009	.234	.246	37.3
44B4821-12-*	12	.007	.009	.270	.284	53.5
44B4821-10-*	10	.008	.010	.330	.347	81.8
44B4821- 8-*	8	.009	.011	.450	.473	142.
44B4821- 6-*	6	.010	.012	.552	.580	221.
44B4821- 4-*	4	.013	.015	.669	.703	339.
44B4821- 2-*	2	.016	.018	.837	.879	546.
44B4821- 0-*	0	.020	.023	1.03	1.08	833.

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 150°C

Maximum continuous conductor temperature

VOLTAGE RATING: 600 volts (rms) at sea level

ACCELERATED AGING: 300 ± 3°C for 7 hours

BLOCKING: 150 ± 3°C for 6 hours

DIELECTRIC WITHSTAND: 2500 volts (rms), 60 Hz, 1 minute

FLAMMABILITY (Procedure 1): 3 seconds (maximum);

3 in. (maximum); no flaming of facial tissue

JACKET COLOR: White preferred

JACKET ELONGATION AND TENSILE STRENGTH:

Elongation, 50% (minimum)

Tensile Strength, 5000 lbf/in² (minimum)

LIFE CYCLE: 200 ± 3°C for 168 hours

LOW TEMPERATURE-COLD BEND: -65 ± 2°C for 4 hours

PART NUMBER:

The "*" in the part numbers above shall be replaced by color code designators with a slash separating the component wire colors and a dash separating the component wire colors from the jacket color.

1/ Example: AWG 20, black and brown component wires; white jacket:
44B4821-20-0/1-9

NOTE: Nominal values are for information only.

Nominal values are not requirements.

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice.

Tyco Electronics also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "Axxx".) OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.

Page 1 of 1

DIMENSIONS ARE IN INCHES, AND UNLESS OTHERWISE DESIGNATED ARE NOMINAL

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN.
REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.



Raychem Wire & Cable
501 Oakside Avenue
Redwood City, CA 94063-3800
Phone: 1-800-227-8816
Fax: 1-650-361-6297

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[44B4821-20-9/96-9CS2275](#) [44B4821-22-9/96-9CS2275](#)