



Nanonics Standard Catalog Part Number Cross-Reference

Revision 1

| TE P/N      | TE CD   | Nanonics P/N    | Part Description  |
|-------------|---------|-----------------|---|
| 1589057-1   | 1589057 | QCM019PC0DC012  | Quick disconnect, circular, metal, 19 position, plug, 28 AWG solid, color coded PTFE wire, 12 inches.   |
| 1589057-3   | 1589057 | QCM019PC2DC003  | Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 3 inches.   |
| 1589057-4   | 1589057 | QCM019PC2DC006  | Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 6 inches.   |
| 1589057-5   | 1589057 | QCM019PC2DC012  | Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 12 inches.  |
| 1589057-6   | 1589057 | QCM019PC2DC020  | Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 20 inches.  |
| 1589057-8   | 1589057 | QCM019PC2DMC46  | Quick disconnect, circular, metal, 19 position, plug, 30AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 46 centimeters.   |
| 1589057-9   | 1589057 | QCM019PC2DXC30  | Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, white PTFE wire, 30 centimeters.   |
| 1-1589057-0 | 1589057 | QCM019PC2DMM01  | Quick disconnect, circular, metal, 19 position, plug, 30AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 1 meter.          |
| 1-1589057-1 | 1589057 | QCM019PC2DCC10  | Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 10 centimeters.   |
| 1-1589057-2 | 1589057 | QCM019PC2DMC150 | Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 150 centimeters. |
| 1-1589057-3 | 1589057 | QCM019PC2DC016  | Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 16 inches.  |
| 1-1589057-4 | 1589057 | QCM019PC2DMC40  | Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 40 centimeters.  |
| 1-1589057-5 | 1589057 | QCM019PC0DC036  | Quick disconnect, circular, metal, 19 position, plug, 28 AWG solid, color coded PTFE wire, 36 inches.   |
| 1-1589057-6 | 1589057 | QCM019PC0DM012  | Quick disconnect, circular, metal, 19 position, plug, 28 AWG solid, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 12 inches.          |
| 1-1589057-7 | 1589057 | QCM019PC2DC084  | Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 84 inches.  |
| 1-1589057-9 | 1589057 | QCM019PC2DC024  | Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 24 inches.  |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[QCM019PC2DCC10](#)