

TE P/N	TE CD	Nanonics P/N	Part Description
1589460-1	1589460	SSL025B2	Dualobe, 1 row, LCP, 25 position, plug, horizontal mount, surface termination, .020 foot tin/lead leadframe.
1589460-2	1589460	SSL037B2EN	Dualobe, 1 row, LCP, 37 position, plug, horizontal mount, surface termination, .020 foot, tin/lead leadframe, adhesive tape, 1.0 captive jackscrews.
1589460-4	1589460	SSL037B2N	Dualobe, 1 row, LCP, 37 position, plug, horizontal mount, surface termination, .020 foot, tin/lead leadframe, 1.0 captive jackscrews.
1589460-5	1589460	SSL051B2	Dualobe, 1 row, LCP, 51 position, plug, horizontal mount, surface termination, .020 foot tin/lead leadframe.
1589460-7	1589460	SSM009B2N	Dualobe, 1 row, metal, 9 position, plug, horizontal mount, surface termination, .020 foot, tin/lead leadframe, 1.0 captive jackscrew.
1589460-9	1589460	SSM037B2	Dualobe, 1 row, metal, 37 position, plug, horizontal mount, surface termination, .020 foot, tin/lead leadframe.
1-1589460-1	1589460	SSM037B2HM	OBSOLETE
1-1589460-2	1589460	SSM037B2N	Dualobe, 1 row, metal, 37 position, plug, horizontal mount, surface termination, .020 foot, tin/lead leadframe, 1.0 captive jackscrew.
1-1589460-3	1589460	SSM015B2N	Dualobe, 1 row, metal, 15 position, plug, horizontal mount, surface termination, .020 foot, tin/lead leadframe, 1.0 captive jackscrews.
1-1589460-5	1589460	SSM009B2Q	Dualobe, 1 row, metal, 9 position, plug, horizontal mount, surface termination, .020 foot, tin/lead leadframe, 1.2 captive jackscrew.
1-1589460-6	1589460	SSM015B2Q	Dualobe, 1 row, metal, 15 position, plug, horizontal mount, surface termination, .020 foot, tin/lead leadframe, 1.2 captive jackscrew.
1-1589460-7	1589460	SSM025B2N	Dualobe, 1 row, metal, 25 position, plug, horizontal mount, surface termination, .020 foot, tin/lead leadframe, 1.0 captive jackscrews.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[SSM015B2Q](#)