

TE P/N	TE CD	Nanonics P/N	Part Description
1589463-1	1589463	SSL009L42HN	Dualobe, 1 row, LCP, 9 position, receptacle, vertical mount, surface termination, 1 side exit, .020 extended leads, tin/lead leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
1589463-2	1589463	SSL009L4CN	Dualobe, 1 row, LCP, 9 position, receptacle, vertical mount, surface termination, .020 foot, tin/lead leadframe, 1.0 x .200 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
1589463-3	1589463	SSL009L4KN	Dualobe, 1 row, LCP, 9 position, receptacle, vertical mount, surface termination, .020 foot, tin/lead leadframe, 1.0 x .200 mounting screw w/ 4 standoffs, thread for 1.0 jackscrews.
1589463-4	1589463	SSL015L4N	Dualobe, 1 row, LCP, 15 position, receptacle, vertical mount, surface termination, .020 foot, tin/lead leadframe, thread for 1.0 jackscrews.
1589463-5	1589463	SSL025L42	Dualobe, 1 row, LCP, 25 position, receptacle, vertical mount, surface termination, 1 side exit, .020 extended leads, tin/lead leadframe.
1589463-6	1589463	SSM009L42KN	Dualobe, 1 row, metal, 9 position, receptacle, vertical mount, surface termination, 1 side exit, .020 extended leads, tin/lead leadframe, 1.0 x .200 mounting screw, thread for 1.0 jackscrews.
1589463-7	1589463	SSM009L44KN	Dualobe, 1 row, metal, 9 position, receptacle, vertical mount, surface termination, 1 side exit, .040 extended leads, tin/lead leadframe, 1.0 x .200 mounting screw, thread for 1.0 jackscrews.
1589463-8	1589463	SSM009L44N	Dualobe, 1 row, metal, 9 position, receptacle, horizontal mount, surface termination, 1 side exit, .040 extended leads, tin/lead leadframe, thread for 1.0 jackscrews.
1589463-9	1589463	SSM009L4KN	Dualobe, 1 row, metal, 9 position, receptacle, vertical mount, surface termination, .020 foot, tin/lead leadframe, 1.0 x .200 mounting screw w/ 4 standoffs, thread for 1.0 jackscrews.
1-1589463-0	1589463	SSM015L44KN	Dualobe, 1 row, metal, 15 position, receptacle, vertical mount, surface termination, 1 side exit, .040 extended leads, tin/lead leadframe, 1.0 x .200 mounting screw w/ 4 standoffs, thread for 1.0 jackscrews.
1-1589463-1	1589463	SSM015L4KN	Dualobe, 1 row, metal, 15 position, receptacle, vertical mount, surface termination, .020 foot, 1.0 x .200 mounting screw w/ 4 standoffs, thread for 1.0 jackscrews.
1-1589463-2	1589463	SSM015L4PQ	Dualobe, 1 row, metal, 15 position, receptacle, vertical mount, surface termination, .020 foot, tin/lead leadframe, 1.2 x .200 mounting screw 4 standoffs, thread for 1.2 jackscrews.
1-1589463-3	1589463	SSM025L44HN	Dualobe, 1 row, metal, 25 position, receptacle, vertical mount, surface termination, 1 side exit, .040 extended leads, tin/lead leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
1-1589463-4	1589463	SSM025L44KN	Dualobe, 1 row, metal, 25 position, receptacle, vertical mount, surface termination, 1 side exit, .040 extended leads, tin/lead leadframe, 1.0 x .200 mounting screw w/ 4 standoffs, thread for 1.0 jackscrews.
1-1589463-5	1589463	SSM025L4HN	Dualobe, 1 row, metal, 25 position, receptacle, vertical mount, surface termination, .020 foot, tin/lead leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
1-1589463-6	1589463	SSM025L4KN	Dualobe, 1 row, metal, 25 position, receptacle, vertical mount, surface termination, .020 foot, tin/lead leadframe, 1.0 x .200 mounting screw w/ 4 standoffs, thread for 1.0 jackscrews.
1-1589463-7	1589463	SSM025L4PQ	Dualobe, 1 row, metal, 25 position, receptacle, vertical mount, surface termination, .020 foot, tin/lead leadframe, 1.2 x .200 mounting screw w/ 4 standoffs, thread for 1.2 jackscrews.
1-1589463-8	1589463	SSM025L4SN	Dualobe, 1 row, metal, 25 position, receptacle, vertical mount, surface termination, .020 foot, tin/lead leadframe, 1.0 x .160 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
1-1589463-9	1589463	SSM037L42KN	Dualobe, 1 row, metal, 37 position, receptacle, vertical mount, surface termination, 1 side exit, .020 extended leads, tin/lead leadframe, 1.0 x .200 mounting screws w/4 standoffs, thread for 1.0 jackscrews.
2-1589463-0	1589463	SSM037L4KN	Dualobe, 1 row, metal, 37 position, receptacle, vertical mount, surface termination, .020 foot, tin/lead leadframe, 1.0 x .200 mounting screw w/ 4 standoffs, thread for 1.0 jackscrews.
2-1589463-1	1589463	SSM051L42KN	Dualobe, 1 row, metal, 51 position, receptacle, vertical mount, surface termination, 1 side exit, .020 extended leads, tin/lead leadframe, 1.0 x .200 mounting screws w/4 standoffs, thread for 1.0 jackscrews.
2-1589463-2	1589463	SSM051L44KN	Dualobe, 1 row, metal, 51 position, receptacle, vertical mount, surface termination, 1 side exit, .040 extended leads, tin/lead leadframe, 1.0 x .200 mounting screw w/ 4 standoffs, thread for 1.0 jackscrews.
2-1589463-3	1589463	SSM051L4KN	Dualobe, 1 row, metal, 51 position, receptacle, vertical mount, surface termination, .020 foot, tin/lead leadframe, 1.0 x .200 mounting screw w/4 standoffs, thread for 1.0 jackscrews.
2-1589463-4	1589463	SSM025L42HN	Dualobe, 1 row, metal, 25 position, receptacle, vertical mount, surface termination, 1 side exit, .020 extended leads, tin/lead leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
2-1589463-5	1589463	SSM037L42IQ	Dualobe, 1 row, metal, 37 position, receptacle, vertical mount, surface termination, 1 side exit, .020 extended leads, tin/lead leadframe, 1.2 x .200 mounting screw, thread for 1.2 jackscrews.
2-1589463-6	1589463	SSL015L4PQ	Dualobe, 1 row, LCP, 15 position, receptacle, vertical mount, surface termination, .020 foot, tin/lead leadframe, 1.2 x .200 mounting screw 4 standoffs, thread for 1.2 jackscrews.
2-1589463-7	1589463	SSM009L4AQ	Dualobe, 1 row, metal, 9 position, receptacle, vertical mount, surface termination, .020 foot, tin/lead leadframe, 1.2 x .160 mounting screw, thread for 1.2 jackscrews.
2-1589463-8	1589463	SSM025L44SN	Dualobe, 1 row, metal, 25 position, receptacle, vertical mount, surface termination, 1 side exit, .040 extended leads, tin/lead leadframe, 1.0 x .160 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
2-1589463-9	1589463	SSL009L42WN	Dualobe, 1 row, LCP, 9 position, receptacle, vertical mount, surface termination, 1 side exit, .020 extended leads, tin/lead leadframe, 1.0 x .160 mounting screw w/ 4 standoffs, thread for 1.0 jackscrews.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[SSL009L42WN](#)