

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - By - ALL RIGHTS RESERVED.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B3	PART 1437648-2 STATUS CORRECTED	20FEB2019	RK	PS

**MATERIALS:**  
 HOUSING: POLYAMIDE, UL94V-0.  
 TERMINALS: COPPER ALLOY, TIN PLATED.  
 SCREWS: STEEL, ZINC PLATED. (UNLESS OTHERWISE NOTED)

**ELECTRICAL:**  
 RATING: 20A, 150V (300V LIMITED RATING)  
 UL & CSA


**MECHANICAL:**  
 WIRE RANGE: 14 - 22 AWG  
 MAXIMUM TIGHTENING TORQUE: 7 IN-LBS.  
 RUNNING TORQUE: 0.5 - 3.5 IN-LBS.

**▲ TERMINALS: COPPER ALLOY, NICKEL PLATED**



OBSOLETE				9.811	30	4DBL-30-006	2-1546937-5
				9.486	29	4DBL-29-006	2-1546937-4
				9.161	28	4DBL-28-006	2-1546937-3
				8.836	27	4DBL-27-006	2-1546937-2
				8.511	26	4DBL-26-006	2-1546937-1
				8.186	25	4DBL-25-006	2-1546937-0
				7.861	24	4DBL-24-006	1-1546937-9
				7.536	23	4DBL-23-006	1-1546937-8
				7.211	22	4DBL-22-006	1-1546937-7
				6.886	21	4DBL-21-006	1-1546937-6
				6.561	20	4DBL-20-006	1-1546937-5
				6.236	19	4DBL-19-006	1-1546937-4
				5.911	18	4DBL-18-006	1-1546937-3
				5.586	17	4DBL-17-006	1-1546937-2
				5.261	16	4DBL-16-006	1-1546937-1
				4.936	15	4DBL-15-006	1-1546937-0
				4.611	14	4DBL-14-006	1546937-9
				4.286	13	4DBL-13-006	1546937-8
				3.961	12	4DBL-12-006	1437648-7
				3.636	11	4DBL-11-006	1546937-7
3.311	10	4DBL-10-006	1546937-6				
2.986	9	4DBL-09-006	1546937-5				
2.661	8	4DBL-08-006	1546937-4				
2.336	7	4DBL-07-006	1546937-3				
2.011	6	4DBL-06-006	1546937-2				
1.686	5	4DBL-05-006	1546937-1				
1.361	4	4DBL-04-006	1437648-5				
1.036	3	4DBL-03-006	1437648-3				
.711	2	-	2-1546937-6				
.711	2	4DBL-02-006	1437648-2				

DIM. A	NO OF POS	CATALOG NUMBER	PART NUMBER
--------	-----------	----------------	-------------



RECOMMENDED HOLE LAYOUT  
 TOLERANCE ±.002, UNLESS OTHERWISE SPECIFIED

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 6/19/07	<b>STE</b> TE Connectivity				
DIMENSIONS: INCHES		CHK S YODER 6/19/07					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S YODER 6/19/07	NAME				
0 PLC ± -		PRODUCT SPEC	4DBL-XX-006 ASSEMBLY				
1 PLC ± -		APPLICATION SPEC					
2 PLC ± .02		WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C-1437648-2	RESTRICTED TO -	
3 PLC ± .008		MATERIAL -	CUSTOMER DRAWING		SCALE NTS	SHEET 1 OF 1	REV B3
4 PLC ANGLES ± 2°			FINISH -				

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## TE Connectivity:

[4DBL-04-006](#) [4DBL-26-006](#) [4DBL-10-006](#) [4DBL-11-006](#) [4DBL-28-006](#) [4DBL-12-006](#) [4DBL-30-006](#) [4DBL-14-006](#)  
[4DBL-09-006](#) [4DBL-13-006](#) [4DBL-29-006](#) [4DBL-27-006](#) [4DBL-25-006](#) [4DBL-07-006](#) [4DBL-08-006](#) [4DBL-19-006](#)  
[4DBL-23-006](#) [4DBL-24-006](#) [4DBL-20-006](#) [4DBL-18-006](#) [4DBL-16-006](#) [4DBL-21-006](#) [4DBL-17-006](#) [2-1546937-7](#)