


P	LTR	DESCRIPTION	DATE	DWN	APVD
	5	INITIAL CUSTOMER DRAWING	01MAY2020	AFK	LS

PRODUCT CODE	PRODUCT PITCH	No. HOLES	LABEL LENGTH	PRINTABLE LENGTH	LABEL HEIGHT
HLX104**TS025	12.7 (1/2")	4	45	25	10.4
HLX104**TS033	12.7 (1/2")	4	53	33	10.4
HLX104**TS038	12.7 (1/2")	4	58	38	10.4
HLX104**TS050	12.7 (1/2")	4	70	50	10.4
HLX104**TS070	12.7 (1/2")	4	90	70	10.4
HLX150**TS025	25.4 (1")	4	45	25	15.0
HLX150**TS033	25.4 (1")	4	53	33	15.0
HLX150**TS038	25.4 (1")	4	58	38	15.0
HLX150**TS050	25.4 (1")	4	70	50	15.0
HLX150**TS070	25.4 (1")	4	90	70	15.0
HLX203**TS025	25.4 (1")	4	45	25	20.3
HLX203**TS033	25.4 (1")	4	53	33	20.3
HLX203**TS038	25.4 (1")	4	58	38	20.3
HLX203**TS050	25.4 (1")	4	70	50	20.3
HLX203**TS070	25.4 (1")	4	90	70	20.3
HLX253**TS025	50.8 (2")	4	45	25	25.3
HLX253**TS033	50.8 (2")	4	53	33	25.3
HLX253**TS038	50.8 (2")	4	58	38	25.3
HLX253**TS050	50.8 (2")	4	70	50	25.3
HLX253**TS070	50.8 (2")	4	90	70	25.3



MATERIAL LIST

- 1. PAPER CARRIER - WHITE
- 2. CABLE LABEL

NOTES:-

- 1. NO ACCUMULATIVE ERROR THROUGH PACK IS ACCEPTABLE
- 2. PACKAGING AS REQUIRED.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN AFK 30APR2020	TE Connectivity			
DIMENSIONS: mm		CHK L.SMITH 01MAY2020				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD L.SMITH 01MAY2020	NAME PRE TAPED LFH THERMAL TRANSFER CABLE LABEL			
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC RW-2529	RESTRICTED TO -			
MATERIAL CROSSLINKED POLYOLEFIN		FINISH -	APPLICATION SPEC 411-121000	SIZE A3	CAGE CODE 0198G	DRAWING NO C-1905A0027
CUSTOMER DRAWING			WEIGHT VARIOUS	SCALE NTS	SHEET 1 OF 1	REV 5

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[EC7642-000](#)