





- 1    DIMENSIONS IN BRACKETS ARE IN INCHES.
- 2    CONTINUOUS STRIP ON REELS.



PART NO.	WIRE		WIRE BARREL CRIMP				TENSILE STRENGTH POUNDS
	QTY	SIZE AWG	WIDTH	CRIMP HEIGHT	CRIMPER	ANVIL	
63315-1	1	14	.120	.071	F	FLAT	50
	1	16		.063			30
	1	18		.057			20

TIN	0.8-2.0 $\text{mm}^2$ [18-14]	0.84-0.76 [033-.030]	63315-2
	0.8-2.0 $\text{mm}^2$ [18-14]	0.84-0.76 [033-.030]	63315-1
FINISH	WIRE SIZE	TAB THK	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

JR RUTH

G YETTER

C MEYERS

—

—

—

—

6/16/87

6/17/87

6/17/87

—

—

—

—

TE Connectivity

NAME

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

RECEPTACLE, FASTON, FLAG, .250 SERIES

A2

00779

C-63315

—

SCALE

SHEET

REV

NTS

1 OF 1

H1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[63315-2 \(Loose Piece\)](#)