




TECHNICAL DATA	T40523X5003-00X	T40523X5004-00X
RATED VOLTAGE	60V	30V
RATED CURRENT	3A	
DEGREE OF PROTECTION	IP67	

7. 产品必须符合ROHS与REACH.

	LABEL	12
TPU	OVER-MOLDING	11
COPPER ALLOY	CONTACT	10
SUS	SPRING	9
BRASS	NUT	8
PA66	HOUSING	7
	CABLE	6
TPU	OVERMOLDING	5
SILICON RUBBER	O-RING	4
BRASS	CONTACT	3
BRASS	NUT	2
PA66,	HOUSING	1

WIRES: 0.25mm ² (24AWG)	STANDARD: -001:0.5 M -002:1.0 M -003:1.5 M -004:3.0 M -005:5.0 M -006:7.0 M -007:10.0 M CUSTOMIZATION: -***:***.0 M -***:***.5 M	FIXED: -40°C~80°C FLXIBLE: -25°C~80°C	GRAY	PUR (UL)	RPC-M8-4FS-***-M12-4MS-PUR 	4	T4052325004-00X
					RPC-M8-3FS-***-M12-3MS-PUR 	3	T4052325003-00X
		FIXED: -10°C~80°C FLXIBLE: -5°C~80°C	BLACK	PVC (UL)	RPC-M8-4FS-***-M12-4MS-PVC 	4	T4052315004-00X
					RPC-M8-3FS-***-M12-3MS-PVC 	3	T4052315003-00X
CABLE CHARACTERISTIC	LENGTH "L"	OPERATION TEMPERATURE	JACKET COLOR	JACKET MATERIAL	TYPE	POS.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Nick Pan 17-Oct-16 CHK Kobby Zhao APVD Xiang Xu		 TE Connectivity	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±0.5 2 PLC ±0.3 3 PLC ±. 4 PLC ±. ANGLES ±.		NAME M8 FEMALE TO M12 MALE CABLE ASSEMBLY DOUBLE ENDED, UNSHIELDED	
MATERIAL - material_2		PRODUCT SPEC 108-106140 APPLICATION SPEC - WEIGHT -		SIZE A2	CAGE CODE C
FINISH - finish_spec_2		CUSTOMER DRAWING		DRAWING NO T40523X500X00X	RESTRICTED TO -
				SCALE 2:1	SHEET 1 of 1
				REV A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T4052325003-006](#)