



THIS DRAWING IS A CONTROLLED DOCUMENT. 104352



- 1 -A- SHALL BE THE INTERSECTION OF THE POST AND THE HOUSING
- 2 ASSEMBLY TO BE CUT TO SIZE AS REQUIRED
- 3 ASSEMBLY MAY NOT EXCEED THE BOW LIMITATIONS AS STATED IN AMP TEST SPEC NO 102-25044
- 4 THE NOTED DIMENSION APPLIES AT THE INTERSECTION OF THE POSTS AND THE HOUSING
- 5 RETENTIVE POSTS PER 115-1166-1 FOR ACTIVE POSITION SIZES OF 6 AND BELOW. (SEE TABLE FOR LOCATIONS)
- 6 RETENTIVE POSTS PER 115-1133-5 FOR ACTIVE POSITION SIZES OF 7 AND ABOVE. (SEE TABLE FOR LOCATIONS)
- 7 .015 (M) FOR KINKED TAILS
- 8 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

RETENTION FEATURE	ROW N	ROW M	QTY	PART NUMBER 2	HOUSING PART NO AS REQD 1	NO OF POSN	ASSEMBLY PART NUMBER	
8	OBSOLETE	15,16	1,2	32	3-147550-7	104832-1	32	2-104352-1
		39,40	1,2	80	1-104818-4	104832-1	80	2-104352-0
		29,30	1,2	60	1-104818-4	104832-1	60	1-104352-9
		24,25	1,2	50	1-104818-4	104832-1	50	1-104352-8
		19,20	1,2	40	1-104818-4	104832-1	40	1-104352-7
		16,17	1,2	34	1-104818-4	104832-1	34	1-104352-6
		14,15	1,2	30	1-104818-4	104832-1	30	1-104352-5
		13,14	1,2	28	1-104818-4	104832-1	28	1-104352-4
		12,13	1,2	26	1-104818-4	104832-1	26	1-104352-3
		11,12	1,2	24	1-104818-4	104832-1	24	1-104352-2
8	OBSOLETE	10,11	1,2	22	1-104818-4	104832-1	22	1-104352-1
	SUPERSEDED	9,10	1,2	20	1-104818-4	104832-1	20	1-104352-0
	OBSOLETE	8,9	1,2	18	1-104818-4	104832-1	18	104352-9
	OBSOLETE	7,8	1,2	16	1-104818-4	104832-1	16	104352-8
		6,7	1,2	14	1-104818-4	104832-1	14	104352-7
	OBSOLETE	5,6	1,2	12	1-104818-4	104832-1	12	104352-6
		4,5	1,2	10	1-104818-4	104832-1	10	104352-5
		3,4	1,2	8	1-104818-4	104832-1	8	104352-4
	OBSOLETE	ALL	ALL	6	1-104818-4	104832-1	6	104352-3
		ALL	ALL	4	1-104818-4	104832-1	4	104352-2
	ALL	ALL	2	1-104818-4	104832-1	2	104352-1	

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE EXPRESS WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA, USA.

LOC AD
DIST 38

DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN H MOLL 2-8-88 MATERIAL - HEAT TREAT -	
0 PLC ± .	1 PLC ± .	2 PLC ± .	3 PLC ± .005	4 PLC ± .	CHK R FEIDT 2-8-88
APVD R FEIDT 2-8-88				Tyco Electronics Tyco Electronics Corporation Harrisburg, Pa	
NAME: HEADER ASSY, MOD II, BREAKAWAY, DBL ROW, .100X.100 VERT, .025 SQ POSTS W/ HOLD-DOWN CONFIG		SCALE: 4:1		DRAWING NO: 104352	
REVISION RECORD		DATE		SHEET 1 OF 1 REV N1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[104352-1](#)