


"BNC" JACK



ϕ .125
3.2 HOLE
(4 PLCS)

.XXX = in
XX.X = mm (REF)

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
01 ₁	REVISED	6/17/96	<i>[Signature]</i> 6/24/96

HOUSING	BRASS PER ASTM-B-16, HALF HARD	NICKEL PLATE QQ-N-290
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A
CENTER CONTACT	BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204
COMPONENT	MATERIAL	FINISH

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES FRAC. DEC. ANGLES ± 1/64 ±.005 ± 1°	DRAWN BY K.L.	DATE 8-3-71	AMP AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599
	CHECKED BY P.R.B.	8-3-71	
	APPD BY B.W.C.	8-3-71	

NOTES:
1. CAPTURED CENTER CONTACT

These drawings and specifications are the property of M/A COM Interconnect Div. and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.	USE ASSY PROCEDURE	TITLE "BNC" FLANGE MOUNT JACK RECEPTACLE - STRAIGHT TERMINAL	
	NO. A.P. <u>N/A</u>	SIZE B	CODE IDENT NO. 26805
		SCALE 4:1	3252-1201-10
			REV 01 ₁
			SHEET 1 OF 1

CUSTOMER DRAWING

AMP PART # 1058016-1
SHEET 1 OF 1 REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1058016-1](#)