


MATED WITH: PASSEND ZU:	LOC A1	DIST -	REVISIONS AENDERUNGEN DESCRIPTION BESCHREIBUNG				DATE	DWN	APVD
-			P	LTR					
PROJEKT NR.:	-		A2	DIN 46320-1 war DIN 46320 Eg00-0555-01			21.08.98	GG	SM
			A3	ECR-17-014011			28MAR18	SG	MKO

Maße nach DIN 46320 -1 / DIN 46259



OBSOLETE	OBSOLETE	OBSOLETE	OBSOLETE
----------	----------	----------	----------

QUANTITY / STÜCK	DESCRIPTION / BENENNUNG	MATERIAL	SURFACE / OBERFLÄCHE	phi A	phi B	phi C	phi D	ITEM NO. POS.	NOTE / BEMERKUNG
2	Druckring PG42	Stahl	verzinkt	-	-	43	52	2	-
2	Druckring PG36	Stahl	verzinkt	-	-	38	45	2	-
2	Druckring PG29	Stahl	verzinkt	-	-	30	35	2	-
2	Druckring PG21	Stahl	verzinkt	-	-	21	26	2	-
2	Druckring PG16	Stahl	verzinkt	-	-	16	20.5	2	-
2	Druckring PG13,5	Stahl	verzinkt	-	-	14	18.5	2	-
2	Druckring PG11	Stahl	verzinkt	-	-	12	17	2	-
1	Dichtring PG42	Neoprene	-	30	51.7	-	-	1	-
1	Dichtring PG36	Neoprene	-	24	44.7	-	-	1	-
1	Dichtring PG29	Neoprene	-	18	34.7	-	-	1	-
1	Dichtring PG21	Neoprene	-	10	25.9	-	-	1	-
1	Dichtring PG16	Neoprene	-	7.5	20.4	-	-	1	-
1	Dichtring PG13,5	Neoprene	-	7.5	18.3	-	-	1	-
1	Dichtring PG11	Neoprene	-	7.5	16.5	-	-	1	-

ORDERING NO. / BESTELLNUMMER		ASD.11.N	
		ASD.13.N	
		ASD.16.N	
		ASD.21.N	
		ASD.29.N	
		ASD.36.N	
		ASD.42.N	

.1997
 RELEASED FOR PUBLICATION
 FREI FUER VEROEFFENTLICHUNG
 ALL RIGHTS RESERVED.
 ALLE RECHTE VORBEHALTEN.
 BY AMP INCORPORATED.
 COPYRIGHT 1997

DIMENSIONS: DIMENSIONEN: mm	DWN Kramer 04.06.98	MATERIAL 1	FINISH OBERFLAECHE/FARBE 2
TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN	CHK Braun 05.06.98	TE Connectivity	
ISO 8015 ISO 2768 - mH - E DIN 16901 - 140	APVD -		
ISO 8015 ISO 2768 - mH - E DIN 16901 - 140	PRODUCT SPEC PRODUKTSPEZ. -	NAME Cut-out Sealing ring Ausschneidbarer Dichtring Set	
APPLICATION SPEC VERARBEITUNGSSPEZ. -	WEIGHT GEWICHT -	SIZE A4	CAGE CODE 00779
ANGLES / WINKEL	CUSTOMER DRAWING	DRAWING NO. ZEICHNUNGS-NR. C=1106050	RESTRICTED TO NUR FUER -
	/KUNDENZEICHNUNG	MASSTAB 1:1	BLATT 1 OF VON 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-1106050-1](#)