







	65.28 [2.570]	67.97 [2.676]	63.91 [2.516]	49	100	6-2267254-0
	52.93 [2.320]	61.62 [2.426]	57.55 [2.266]	44	90	5-2267254-9
	52.58 [2.070]	55.27 [2.176]	51.21 [2.016]	39	80	5-2267254-8
	46.23 [1.820]	48.92 [1.926]	44.86 [1.766]	34	70	5-2267254-7
	39.88 [1.570]	42.57 [1.676]	38.51 [1.516]	29	60	5-2267254-6
	33.53 [1.320]	36.22 [1.426]	32.16 [1.266]	24	50	5-2267254-5
	27.18 [1.070]	29.87 [1.176]	25.81 [1.016]	19	40	5-2267254-4
	20.83 [.820]	23.52 [.926]	19.46 [.766]	14	30	5-2267254-3
	14.48 [.570]	17.17 [.676]	13.11 [.516]	9	20	5-2267254-2
	8.12 [.320]	10.82 [.426]	6.75 [.266]	4	10	5-2267254-1
	65.28 [2.570]	67.97 [2.676]	63.91 [2.516]	49	100	1-2267254-0
	52.93 [2.320]	61.62 [2.426]	57.55 [2.266]	44	90	2267254-9
	52.58 [2.070]	55.27 [2.176]	51.21 [2.016]	39	80	2267254-8
	46.23 [1.820]	48.92 [1.926]	44.86 [1.766]	34	70	2267254-7
	39.88 [1.570]	42.57 [1.676]	38.51 [1.516]	29	60	2267254-6
	33.53 [1.320]	36.22 [1.426]	32.16 [1.266]	24	50	2267254-5
	27.18 [1.070]	29.87 [1.176]	25.81 [1.016]	19	40	2267254-4
	20.83 [.820]	23.52 [.926]	19.46 [.766]	14	30	2267254-3
	14.48 [.570]	17.17 [.676]	13.11 [.516]	9	20	2267254-2
	8.12 [.320]	10.82 [.426]	6.75 [.266]	4	10	2267254-1
FINISH	D	C	B	A	NUMBER OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: RVL.S 04APH2019 CHK: J. OLSON 04APR2019 APVD: J. OLSON 04APR2019		 TE Connectivity	
DIMENSIONS: mm [INCH]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		NAME ASSY, RECEPTACLE, VERT. DOUBLE ROW, THROUGH HOLE, AMPMODU 50/50 GRID CONNECTOR	
		PRODUCT SPEC 108-1332 APPLICATION SPEC 114-7010		SIZE CAGE CODE DRAWING NO A100779 C-2267254	
MATERIAL FINISH 6		WEIGHT -		RESTRICTED TO -	
SEE TABLE		CUSTOMER DRAWING		SCALE 10:1 SHEET 1 OF 1 REV A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-2267254-8](#)