



- NOTES :**
- ▲ MATERIALS AND FINISH:
    - HOUSING: PA66
    - CONTACTS: BRASS, FINISH: TIN OVER NICKEL UNDERPLATE
  - 2. MUST COMPLY WITH DIRECTIVE 2002/95/EC (ROHS)
  - 3. WIRE TYPES AND SIZES ACCEPTED
  - WIRE RANGE: 20AWG~28AWG.
  - STRIP LENGTH: 5.5mm~6.5mm
  - 4. PACKAGED IN TRAY.
  - 5. CURRENT RATING: 4Amp AC150V.
  - 6. OPERATION TEMPERATURE: -40°C TO +105°C
  - 7. THIS PART NO. IS THE SAME STRUCTURE AS THE SERIES: 2834084
  - THE DATASHEET AND MORE DETAILS PLEASE FOLLOW THE SERIES: 2834084

REVISONS		DATE	DM	AP/3
P	1/1			
A	1			

④	WIRE PROTECTOR	
③	CONTACT	
②	COVER	
①	HOUSING	
21.50	8 POSN	2834084-7
19.00	7 POSN	2834084-6
16.50	6 POSN	2834084-5
14.00	5 POSN	2834084-4
11.50	4 POSN	2834084-3
9.00	3 POSN	2834084-2
6.50	2 POSN	2834084-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

CONTROLLED BY: **STE** (Solderless Technology)

DATE: 08DEC2015

VERSION: 1.1

DESCRIPTION: 2.5 45Entry Screwless Connector

SIZE: A2 | CODE: C-2834084

SCALE: 1:1

DATE: 11/11/15

REV: A

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2834084-3](#)